

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585074

Luminaire Tested: **HC860D010-HM86080830-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC860D010-HM86080830-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5147.0 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 56
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585074

CATALOG NUMBER: HC860D010-HM86080830-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P585074

CATALOG NUMBER: HC860D010-HM86080830-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120817
5°	119241
10°	114874
15°	110384
20°	107332
25°	104100
30°	93414
35°	61240
40°	33858
45°	28224
50°	25733
55°	24564
60°	22844
65°	20715
70°	18717
75°	16906
80°	15361
85°	14683



TEST NUMBER: P585074

CATALOG NUMBER: HC860D010-HM86080830-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.9	7.0
10°-20°	975.5	19.0
20°-30°	1388.3	27.0
30°-40°	1027.5	20.0
40°-50°	508.9	9.9
50°-60°	406.2	7.9
60°-70°	282.0	5.5
70°-80°	151.9	3.0
80°-90°	44.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2725.8	53.0
0°-40°	3753.3	72.9
0°-60°	4668.4	90.7
0°-90°	5147.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5147.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3918	
5°	3852	362
15°	3458	976
25°	3060	1388
35°	1627	1028
45°	647	509
55°	457	406
65°	284	282
75°	142	152
85°	42	45
90°	0	



TEST NUMBER: P585074

CATALOG NUMBER: HC860D010-HM86080830-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3918.0
2.5°	3900.7
5°	3852.2
7.5°	3776.1
10°	3668.7
12.5°	3558.0
15°	3457.7
17.5°	3360.8
20°	3270.8
22.5°	3180.7
25°	3059.6
27.5°	2883.2
30°	2623.5
32.5°	2225.5
35°	1626.8
37.5°	1111.1
40°	841.1
42.5°	720.0
45°	647.2
47.5°	588.3
50°	536.4
52.5°	491.5
55°	456.9
57.5°	415.3
60°	370.4
62.5°	325.4
65°	283.9
67.5°	242.3
70°	207.6
72.5°	173.0
75°	141.9
77.5°	114.2
80°	86.5
82.5°	62.3
85°	41.5
87.5°	17.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)