

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585114

Luminaire Tested: **HC860D010-HM86080840-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC860D010-HM86080840-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6696.6 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 56
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585114

CATALOG NUMBER: HC860D010-HM86080840-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P585114

CATALOG NUMBER: HC860D010-HM86080840-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133879
5°	133716
10°	132393
15°	130809
20°	129594
25°	128142
30°	120910
35°	98455
40°	54395
45°	36305
50°	32204
55°	30230
60°	29843
65°	29580
70°	26723
75°	23888
80°	20883
85°	18539



TEST NUMBER: P585114

CATALOG NUMBER: HC860D010-HM86080840-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	409.4	6.1
10°-20°	1157.0	17.3
20°-30°	1719.1	25.7
30°-40°	1548.2	23.1
40°-50°	686.3	10.2
50°-60°	508.3	7.6
60°-70°	395.3	5.9
70°-80°	214.3	3.2
80°-90°	58.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3285.5	49.1
0°-40°	4833.6	72.2
0°-60°	6028.3	90.0
0°-90°	6696.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6696.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4342	
5°	4320	409
15°	4098	1157
25°	3766	1719
35°	2615	1548
45°	832	686
55°	562	508
65°	405	395
75°	200	214
85°	52	59
90°	0	



TEST NUMBER: P585114

CATALOG NUMBER: HC860D010-HM86080840-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4341.6
2.5°	4332.9
5°	4319.8
7.5°	4284.9
10°	4228.2
12.5°	4162.9
15°	4097.5
17.5°	4032.1
20°	3949.2
22.5°	3866.4
25°	3766.2
27.5°	3613.6
30°	3395.7
32.5°	3081.8
35°	2615.4
37.5°	1952.8
40°	1351.3
42.5°	998.3
45°	832.5
47.5°	736.7
50°	671.3
52.5°	610.3
55°	562.3
57.5°	523.1
60°	483.9
62.5°	449.0
65°	405.4
67.5°	353.1
70°	296.4
72.5°	248.4
75°	200.5
77.5°	157.0
80°	117.6
82.5°	82.8
85°	52.4
87.5°	21.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)