

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593510

Luminaire Tested: **HC807D010-HM80520950-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593510
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC807D010-HM80520950-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 940.0 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593510

CATALOG NUMBER: HC807D010-HM80520950-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P593510

CATALOG NUMBER: HC807D010-HM80520950-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18792
5°	18767
10°	18587
15°	18363
20°	18193
25°	17989
30°	16974
35°	13819
40°	7632
45°	5098
50°	4524
55°	4242
60°	4188
65°	4152
70°	3751
75°	3360
80°	2930
85°	2583



TEST NUMBER: P593510

CATALOG NUMBER: HC807D010-HM80520950-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	6.1
10°-20°	162.4	17.3
20°-30°	241.3	25.7
30°-40°	217.3	23.1
40°-50°	96.4	10.3
50°-60°	71.4	7.6
60°-70°	55.5	5.9
70°-80°	30.1	3.2
80°-90°	8.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.2	49.1
0°-40°	678.5	72.2
0°-60°	846.2	90.0
0°-90°	940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	940.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	609	
5°	606	57
15°	575	162
25°	529	241
35°	367	217
45°	117	96
55°	79	71
65°	57	55
75°	28	30
85°	7	8
90°	0	



TEST NUMBER: P593510

CATALOG NUMBER: HC807D010-HM80520950-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	609.4
2.5°	608.1
5°	606.3
7.5°	601.4
10°	593.6
12.5°	584.4
15°	575.2
17.5°	566.0
20°	554.4
22.5°	542.8
25°	528.7
27.5°	507.3
30°	476.7
32.5°	432.6
35°	367.1
37.5°	274.1
40°	189.6
42.5°	140.2
45°	116.9
47.5°	103.4
50°	94.3
52.5°	85.7
55°	78.9
57.5°	73.4
60°	67.9
62.5°	63.0
65°	56.9
67.5°	49.6
70°	41.6
72.5°	34.9
75°	28.2
77.5°	22.0
80°	16.5
82.5°	11.6
85°	7.3
87.5°	3.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)