

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585140

Luminaire Tested: **HC860D010-HM86080930-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC860D010-HM86080930-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4398.6 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 56
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585140

CATALOG NUMBER: HC860D010-HM86080930-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P585140

CATALOG NUMBER: HC860D010-HM86080930-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	350008
5°	296528
10°	215145
15°	161568
20°	127481
25°	102831
30°	76198
35°	30872
40°	13018
45°	6982
50°	3137
55°	1581
60°	1011
65°	715
70°	595
75°	381
80°	568
85°	1132



TEST NUMBER: P585140

CATALOG NUMBER: HC860D010-HM86080930-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	822.5	18.7
10°-20°	1421.5	32.3
20°-30°	1374.3	31.2
30°-40°	603.6	13.7
40°-50°	130.5	3.0
50°-60°	29.3	0.7
60°-70°	10.1	0.2
70°-80°	3.8	0.1
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3618.3	82.3
0°-40°	4221.9	96.0
0°-60°	4381.7	99.6
0°-90°	4398.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4398.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11350	
5°	9580	822
15°	5061	1421
25°	3022	1374
35°	820	604
45°	160	130
55°	29	29
65°	10	10
75°	3	4
85°	3	3
90°	0	



TEST NUMBER: P585140

CATALOG NUMBER: HC860D010-HM86080930-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	11350.5
1°	11265.5
2°	11033.5
3°	10615.3
4°	10115.4
5°	9579.6
6°	8994.8
7°	8406.7
8°	7854.5
9°	7341.5
10°	6871.0
11°	6426.7
12°	6028.1
13°	5665.4
14°	5345.2
15°	5061.0
17.5°	4423.9
20°	3884.8
22.5°	3411.1
25°	3022.3
27.5°	2626.9
30°	2140.0
32.5°	1454.0
35°	820.1
37.5°	483.5
40°	323.4
42.5°	228.7
45°	160.1
47.5°	104.5
50°	65.4
52.5°	39.2
55°	29.4
57.5°	22.8
60°	16.4
62.5°	13.0
65°	9.8
67.5°	6.6
70°	6.6
72.5°	3.2
75°	3.2
77.5°	3.2
80°	3.2
82.5°	3.2



TEST NUMBER: P585140

CATALOG NUMBER: HC860D010-HM86080930-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







85°	3.2
87.5°	3.2



(END OF REPORT)