

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585233

Luminaire Tested: **HC880D010-HM86080835-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585233  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC880D010-HM86080835-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7638.0 lumens  
Efficiency: N/A  
Efficacy: 109.1 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585233

CATALOG NUMBER: HC880D010-HM86080835-81WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P585233

CATALOG NUMBER: HC880D010-HM86080835-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	152698
5°	152514
10°	151008
15°	149200
20°	147817
25°	146157
30°	137905
35°	112296
40°	62043
45°	41416
50°	36733
55°	34477
60°	34037
65°	33739
70°	30474
75°	27260
80°	23831
85°	21122



TEST NUMBER: P585233

CATALOG NUMBER: HC880D010-HM86080835-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	467.0	6.1
10°-20°	1319.6	17.3
20°-30°	1960.8	25.7
30°-40°	1765.8	23.1
40°-50°	782.9	10.2
50°-60°	579.7	7.6
60°-70°	450.8	5.9
70°-80°	244.4	3.2
80°-90°	66.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3747.4	49.1
0°-40°	5513.2	72.2
0°-60°	6875.8	90.0
0°-90°	7638.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7638.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4952	
5°	4927	467
15°	4674	1320
25°	4296	1961
35°	2983	1766
45°	950	783
55°	641	580
65°	462	451
75°	229	244
85°	60	67
90°	0	



TEST NUMBER: P585233

CATALOG NUMBER: HC880D010-HM86080835-81WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4951.9
2.5°	4942.1
5°	4927.1
7.5°	4887.4
10°	4822.7
12.5°	4748.2
15°	4673.6
17.5°	4598.9
20°	4504.5
22.5°	4410.0
25°	4295.7
27.5°	4121.7
30°	3873.0
32.5°	3515.2
35°	2983.1
37.5°	2227.4
40°	1541.3
42.5°	1138.6
45°	949.7
47.5°	840.3
50°	765.7
52.5°	696.0
55°	641.3
57.5°	596.6
60°	551.9
62.5°	512.1
65°	462.4
67.5°	402.7
70°	338.0
72.5°	283.3
75°	228.8
77.5°	178.9
80°	134.2
82.5°	94.4
85°	59.7
87.5°	24.9
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)