

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585179

Luminaire Tested: **HC860D010-HM86080940-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC860D010-HM86080940-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5707.7 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585179

CATALOG NUMBER: HC860D010-HM86080940-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P585179

CATALOG NUMBER: HC860D010-HM86080940-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106940
5°	106052
10°	104651
15°	105848
20°	114306
25°	124998
30°	123484
35°	102434
40°	60288
45°	39388
50°	30530
55°	20284
60°	9874
65°	3057
70°	1028
75°	905
80°	675
85°	1344



TEST NUMBER: P585179

CATALOG NUMBER: HC860D010-HM86080940-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	324.5	5.7
10°-20°	952.5	16.7
20°-30°	1665.4	29.2
30°-40°	1620.0	28.4
40°-50°	736.7	12.9
50°-60°	341.6	6.0
60°-70°	57.2	1.0
70°-80°	7.0	0.1
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2942.4	51.6
0°-40°	4562.5	79.9
0°-60°	5640.8	98.8
0°-90°	5707.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5707.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3468	
5°	3426	324
15°	3316	953
25°	3674	1665
35°	2721	1620
45°	903	737
55°	377	342
65°	42	57
75°	8	7
85°	4	3
90°	0	



TEST NUMBER: P585179

CATALOG NUMBER: HC860D010-HM86080940-81WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3468.0
2.5°	3460.4
5°	3426.1
7.5°	3388.0
10°	3342.2
12.5°	3308.0
15°	3315.6
17.5°	3376.6
20°	3483.3
22.5°	3605.2
25°	3673.8
27.5°	3635.7
30°	3468.0
32.5°	3174.6
35°	2721.1
37.5°	2096.1
40°	1497.7
42.5°	1116.6
45°	903.2
47.5°	762.2
50°	636.4
52.5°	506.9
55°	377.3
57.5°	259.2
60°	160.1
62.5°	87.7
65°	41.9
67.5°	19.0
70°	11.4
72.5°	7.6
75°	7.6
77.5°	3.8
80°	3.8
82.5°	3.8
85°	3.8
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)