

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585174

Luminaire Tested: **HC860D010-HM86080940-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585174
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC860D010-HM86080940-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5158.9 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 56
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585174

CATALOG NUMBER: HC860D010-HM86080940-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P585174

CATALOG NUMBER: HC860D010-HM86080940-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	410502
5°	347782
10°	252331
15°	189492
20°	149513
25°	120598
30°	89369
35°	36206
40°	15272
45°	8190
50°	3675
55°	1855
60°	1178
65°	839
70°	685
75°	453
80°	675
85°	1344



TEST NUMBER: P585174

CATALOG NUMBER: HC860D010-HM86080940-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	964.7	18.7
10°-20°	1667.1	32.3
20°-30°	1611.8	31.2
30°-40°	707.9	13.7
40°-50°	153.0	3.0
50°-60°	34.4	0.7
60°-70°	11.8	0.2
70°-80°	4.5	0.1
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4243.6	82.3
0°-40°	4951.6	96.0
0°-60°	5139.0	99.6
0°-90°	5158.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5158.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13312	
5°	11235	965
15°	5936	1667
25°	3544	1612
35°	962	708
45°	188	153
55°	34	34
65°	12	12
75°	4	5
85°	4	4
90°	0	



TEST NUMBER: P585174

CATALOG NUMBER: HC860D010-HM86080940-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	13312.3
1°	13212.7
2°	12940.6
3°	12450.0
4°	11863.8
5°	11235.4
6°	10549.5
7°	9859.6
8°	9212.1
9°	8610.5
10°	8058.6
11°	7537.5
12°	7070.0
13°	6644.6
14°	6269.1
15°	5935.7
17.5°	5188.5
20°	4556.2
22.5°	4000.6
25°	3544.5
27.5°	3080.8
30°	2509.9
32.5°	1705.2
35°	961.8
37.5°	567.1
40°	379.4
42.5°	268.3
45°	187.8
47.5°	122.6
50°	76.6
52.5°	46.0
55°	34.5
57.5°	26.9
60°	19.1
62.5°	15.3
65°	11.5
67.5°	7.6
70°	7.6
72.5°	3.8
75°	3.8
77.5°	3.8
80°	3.8
82.5°	3.8



TEST NUMBER: P585174

CATALOG NUMBER: HC860D010-HM86080940-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







85°	3.8
87.5°	3.8



(END OF REPORT)