

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593878

Luminaire Tested: **HC860D010-HM86080950-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593878
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC860D010-HM86080950-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6157.2 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 56
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593878

CATALOG NUMBER: HC860D010-HM86080950-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P593878

CATALOG NUMBER: HC860D010-HM86080950-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84		
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79		
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75		
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71		
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67		
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64		
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61		
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	367886
5°	351013
10°	303050
15°	231731
20°	177304
25°	140275
30°	105962
35°	56372
40°	21471
45°	10300
50°	4390
55°	1844
60°	703
65°	555
70°	343
75°	0
80°	0
85°	0



TEST NUMBER: P593878

CATALOG NUMBER: HC860D010-HM86080950-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1029.4	16.7
10°-20°	2026.4	32.9
20°-30°	1887.3	30.7
30°-40°	973.8	15.8
40°-50°	198.3	3.2
50°-60°	33.9	0.6
60°-70°	6.6	0.1
70°-80°	1.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4943.1	80.3
0°-40°	5916.9	96.1
0°-60°	6149.2	99.9
0°-90°	6157.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6157.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11930	
5°	11340	###
15°	7259	2026
25°	4123	1887
35°	1498	974
45°	236	198
55°	34	34
65°	8	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P593878

CATALOG NUMBER: HC860D010-HM86080950-81MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	11930.3
2.5°	11770.3
5°	11339.8
7.5°	10631.0
10°	9678.4
12.5°	8428.6
15°	7258.8
17.5°	6245.2
20°	5403.1
22.5°	4717.3
25°	4122.8
27.5°	3558.9
30°	2975.9
32.5°	2282.5
35°	1497.5
37.5°	868.7
40°	533.4
42.5°	350.5
45°	236.2
47.5°	148.6
50°	91.5
52.5°	53.4
55°	34.3
57.5°	15.2
60°	11.4
62.5°	7.6
65°	7.6
67.5°	3.8
70°	3.8
72.5°	3.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)