

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583589

Luminaire Tested: **HC807D010-HM80520830-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583589  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC807D010-HM80520830-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1025.2 lumens  
Efficiency: N/A  
Efficacy: 128.2 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583589

CATALOG NUMBER: HC807D010-HM80520830-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P583589

CATALOG NUMBER: HC807D010-HM80520830-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18005
5°	17882
10°	17832
15°	18305
20°	19814
25°	21245
30°	20769
35°	17294
40°	10627
45°	7357
50°	5613
55°	3683
60°	2307
65°	1729
70°	1731
75°	2002
80°	2202
85°	1981



TEST NUMBER: P583589

CATALOG NUMBER: HC807D010-HM80520830-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.9	5.4
10°-20°	164.6	16.1
20°-30°	283.3	27.6
30°-40°	274.5	26.8
40°-50°	135.2	13.2
50°-60°	63.8	6.2
60°-70°	25.2	2.5
70°-80°	17.3	1.7
80°-90°	6.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	502.8	49.0
0°-40°	777.3	75.8
0°-60°	976.3	95.2
0°-90°	1025.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1025.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	584	
5°	578	55
15°	573	165
25°	624	283
35°	459	274
45°	169	135
55°	68	64
65°	24	25
75°	17	17
85°	6	6
90°	0	



TEST NUMBER: P583589

CATALOG NUMBER: HC807D010-HM80520830-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	583.9
2.5°	582.1
5°	577.7
7.5°	573.4
10°	569.5
12.5°	568.9
15°	573.4
17.5°	586.4
20°	603.8
22.5°	619.4
25°	624.4
27.5°	613.2
30°	583.3
32.5°	534.0
35°	459.4
37.5°	356.7
40°	264.0
42.5°	204.8
45°	168.7
47.5°	142.0
50°	117.0
52.5°	92.1
55°	68.5
57.5°	49.8
60°	37.4
62.5°	29.3
65°	23.7
67.5°	20.6
70°	19.2
72.5°	18.0
75°	16.8
77.5°	14.9
80°	12.4
82.5°	9.3
85°	5.6
87.5°	2.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)