

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585259

Luminaire Tested: **HC880D010-HM86080927-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585259
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC880D010-HM86080927-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4911.5 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 70
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585259

CATALOG NUMBER: HC880D010-HM86080927-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P585259

CATALOG NUMBER: HC880D010-HM86080927-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 100 | 99 | 98 | 97 | 96 | 95 | 95 | 95 | 95 |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 92 | 91 | 89 | 89 | 89 | 89 |
| 3 | 104 | 99 | 94 | 91 | 102 | 97 | 93 | 90 | 95 | 91 | 88 | 92 | 90 | 87 | 90 | 88 | 86 | 84 | 84 | 84 | 84 |
| 4 | 100 | 93 | 88 | 84 | 98 | 92 | 87 | 84 | 90 | 86 | 83 | 88 | 85 | 82 | 86 | 83 | 81 | 80 | 80 | 80 | 80 |
| 5 | 96 | 88 | 83 | 79 | 94 | 87 | 82 | 79 | 86 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 77 | 75 | 75 | 75 | 75 |
| 6 | 92 | 84 | 78 | 75 | 90 | 83 | 78 | 74 | 81 | 77 | 74 | 80 | 76 | 73 | 79 | 76 | 73 | 72 | 72 | 72 | 72 |
| 7 | 88 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 70 | 77 | 73 | 70 | 76 | 72 | 69 | 68 | 68 | 68 | 68 |
| 8 | 84 | 76 | 70 | 67 | 83 | 75 | 70 | 67 | 74 | 70 | 66 | 73 | 69 | 66 | 72 | 69 | 66 | 65 | 65 | 65 | 65 |
| 9 | 81 | 72 | 67 | 64 | 80 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 63 | 69 | 66 | 63 | 62 | 62 | 62 | 62 |
| 10 | 78 | 69 | 64 | 61 | 77 | 69 | 64 | 61 | 68 | 63 | 60 | 67 | 63 | 60 | 67 | 63 | 60 | 59 | 59 | 59 | 59 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 390798 |
| 5° | 331088 |
| 10° | 240223 |
| 15° | 180397 |
| 20° | 142340 |
| 25° | 114814 |
| 30° | 85082 |
| 35° | 34467 |
| 40° | 14536 |
| 45° | 7793 |
| 50° | 3502 |
| 55° | 1763 |
| 60° | 1122 |
| 65° | 795 |
| 70° | 658 |
| 75° | 441 |
| 80° | 657 |
| 85° | 1309 |



TEST NUMBER: P585259

CATALOG NUMBER: HC880D010-HM86080927-81NDH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 918.4 | 18.7 |
| 10°-20° | 1587.1 | 32.3 |
| 20°-30° | 1534.5 | 31.2 |
| 30°-40° | 673.9 | 13.7 |
| 40°-50° | 145.7 | 3.0 |
| 50°-60° | 32.7 | 0.7 |
| 60°-70° | 11.2 | 0.2 |
| 70°-80° | 4.4 | 0.1 |
| 80°-90° | 3.5 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 4040.0 | 82.3 |
| 0°-40° | 4713.9 | 96.0 |
| 0°-60° | 4892.3 | 99.6 |
| 0°-90° | 4911.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 4911.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 12673 | |
| 5° | 10696 | 918 |
| 15° | 5651 | 1587 |
| 25° | 3374 | 1535 |
| 35° | 916 | 674 |
| 45° | 179 | 146 |
| 55° | 33 | 33 |
| 65° | 11 | 11 |
| 75° | 4 | 4 |
| 85° | 4 | 4 |
| 90° | 0 | |



TEST NUMBER: P585259

CATALOG NUMBER: HC880D010-HM86080927-81NDH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 12673.3 |
| 1° | 12578.5 |
| 2° | 12319.5 |
| 3° | 11852.5 |
| 4° | 11294.4 |
| 5° | 10696.1 |
| 6° | 10043.1 |
| 7° | 9386.4 |
| 8° | 8769.9 |
| 9° | 8197.2 |
| 10° | 7671.9 |
| 11° | 7175.7 |
| 12° | 6730.7 |
| 13° | 6325.7 |
| 14° | 5968.2 |
| 15° | 5650.8 |
| 17.5° | 4939.5 |
| 20° | 4337.6 |
| 22.5° | 3808.6 |
| 25° | 3374.5 |
| 27.5° | 2933.0 |
| 30° | 2389.5 |
| 32.5° | 1623.3 |
| 35° | 915.6 |
| 37.5° | 539.9 |
| 40° | 361.1 |
| 42.5° | 255.4 |
| 45° | 178.7 |
| 47.5° | 116.8 |
| 50° | 73.0 |
| 52.5° | 43.8 |
| 55° | 32.8 |
| 57.5° | 25.6 |
| 60° | 18.2 |
| 62.5° | 14.6 |
| 65° | 10.9 |
| 67.5° | 7.3 |
| 70° | 7.3 |
| 72.5° | 3.7 |
| 75° | 3.7 |
| 77.5° | 3.7 |
| 80° | 3.7 |
| 82.5° | 3.7 |



TEST NUMBER: P585259

CATALOG NUMBER: HC880D010-HM86080927-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







| | |
|-------|-----|
| 85° | 3.7 |
| 87.5° | 3.7 |



(END OF REPORT)