

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583602

Luminaire Tested: **HC807D010-HM80520835-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC807D010-HM80520835-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 970.0 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583602

CATALOG NUMBER: HC807D010-HM80520835-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P583602

CATALOG NUMBER: HC807D010-HM80520835-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18175
5°	18025
10°	17788
15°	17992
20°	19427
25°	21245
30°	20987
35°	17410
40°	10245
45°	6698
50°	5186
55°	3451
60°	1677
65°	525
70°	171
75°	155
80°	107
85°	212



TEST NUMBER: P583602

CATALOG NUMBER: HC807D010-HM80520835-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.2	5.7
10°-20°	161.9	16.7
20°-30°	283.1	29.2
30°-40°	275.3	28.4
40°-50°	125.2	12.9
50°-60°	58.1	6.0
60°-70°	9.7	1.0
70°-80°	1.2	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	500.1	51.6
0°-40°	775.4	79.9
0°-60°	958.7	98.8
0°-90°	970.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	970.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	589	
5°	582	55
15°	564	162
25°	624	283
35°	462	275
45°	154	125
55°	64	58
65°	7	10
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P583602

CATALOG NUMBER: HC807D010-HM80520835-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	589.4
2.5°	588.2
5°	582.3
7.5°	575.9
10°	568.1
12.5°	562.2
15°	563.6
17.5°	573.8
20°	592.0
22.5°	612.8
25°	624.4
27.5°	617.9
30°	589.4
32.5°	539.5
35°	462.5
37.5°	356.2
40°	254.5
42.5°	189.8
45°	153.6
47.5°	129.5
50°	108.1
52.5°	86.2
55°	64.2
57.5°	44.1
60°	27.2
62.5°	14.9
65°	7.2
67.5°	3.2
70°	1.9
72.5°	1.3
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)