

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583606

Luminaire Tested: **HC807D010-HM80520835-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583606  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC807D010-HM80520835-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1066.6 lumens  
Efficiency: N/A  
Efficacy: 133.3 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583606

CATALOG NUMBER: HC807D010-HM80520835-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P583606

CATALOG NUMBER: HC807D010-HM80520835-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18730
5°	18603
10°	18555
15°	19040
20°	20615
25°	22099
30°	21606
35°	17990
40°	11054
45°	7653
50°	5843
55°	3828
60°	2393
65°	1795
70°	1812
75°	2073
80°	2291
85°	2087



TEST NUMBER: P583606

CATALOG NUMBER: HC807D010-HM80520835-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.1	5.4
10°-20°	171.2	16.1
20°-30°	294.7	27.6
30°-40°	285.6	26.8
40°-50°	140.7	13.2
50°-60°	66.4	6.2
60°-70°	26.2	2.5
70°-80°	18.0	1.7
80°-90°	6.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	523.1	49.0
0°-40°	808.6	75.8
0°-60°	1015.7	95.2
0°-90°	1066.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1066.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	607	
5°	601	57
15°	596	171
25°	650	295
35°	478	286
45°	176	141
55°	71	66
65°	25	26
75°	17	18
85°	6	7
90°	0	



TEST NUMBER: P583606

CATALOG NUMBER: HC807D010-HM80520835-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	607.4
2.5°	605.5
5°	601.0
7.5°	596.4
10°	592.6
12.5°	591.9
15°	596.4
17.5°	610.0
20°	628.2
22.5°	644.3
25°	649.5
27.5°	637.9
30°	606.8
32.5°	555.7
35°	477.9
37.5°	371.0
40°	274.6
42.5°	213.1
45°	175.5
47.5°	147.7
50°	121.8
52.5°	95.8
55°	71.2
57.5°	51.9
60°	38.8
62.5°	30.5
65°	24.6
67.5°	21.4
70°	20.1
72.5°	18.8
75°	17.4
77.5°	15.5
80°	12.9
82.5°	9.7
85°	5.9
87.5°	2.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)