

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585266

Luminaire Tested: **HC880D010-HM86080927-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC880D010-HM86080927-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5771.1 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585266

CATALOG NUMBER: HC880D010-HM86080927-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P585266

CATALOG NUMBER: HC880D010-HM86080927-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132124
5°	129147
10°	125185
15°	122652
20°	121555
25°	119734
30°	113418
35°	94235
40°	55494
45°	36706
50°	28889
55°	21263
60°	14771
65°	8997
70°	3922
75°	1728
80°	1296
85°	0



TEST NUMBER: P585266

CATALOG NUMBER: HC880D010-HM86080927-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	392.9	6.8
10°-20°	1086.2	18.8
20°-30°	1609.3	27.9
30°-40°	1487.0	25.8
40°-50°	685.6	11.9
50°-60°	360.6	6.2
60°-70°	127.4	2.2
70°-80°	20.0	0.3
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3088.3	53.5
0°-40°	4575.4	79.3
0°-60°	5621.7	97.4
0°-90°	5771.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5771.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4285	
5°	4172	393
15°	3842	1086
25°	3519	1609
35°	2503	1487
45°	842	686
55°	396	361
65°	123	127
75°	14	20
85°	0	2
90°	0	



TEST NUMBER: P585266

CATALOG NUMBER: HC880D010-HM86080927-81WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4284.7
2.5°	4248.3
5°	4172.2
7.5°	4088.7
10°	3998.0
12.5°	3911.0
15°	3842.0
17.5°	3780.3
20°	3704.2
22.5°	3620.7
25°	3519.1
27.5°	3381.3
30°	3185.3
32.5°	2906.0
35°	2503.3
37.5°	1922.9
40°	1378.6
42.5°	1034.0
45°	841.7
47.5°	714.7
50°	602.2
52.5°	493.4
55°	395.5
57.5°	312.0
60°	239.5
62.5°	181.4
65°	123.3
67.5°	72.5
70°	43.5
72.5°	25.4
75°	14.5
77.5°	10.9
80°	7.3
82.5°	3.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)