

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583603

Luminaire Tested: **HC807D010-HM80520835-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC807D010-HM80520835-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1087.9 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583603

CATALOG NUMBER: HC807D010-HM80520835-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P583603

CATALOG NUMBER: HC807D010-HM80520835-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26100
5°	25401
10°	25206
15°	24831
20°	24077
25°	23181
30°	21652
35°	17919
40°	10820
45°	7287
50°	5253
55°	2995
60°	1320
65°	474
70°	171
75°	71
80°	0
85°	0



TEST NUMBER: P583603

CATALOG NUMBER: HC807D010-HM80520835-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	7.2
10°-20°	218.6	20.1
20°-30°	311.8	28.7
30°-40°	283.9	26.1
40°-50°	134.0	12.3
50°-60°	52.7	4.8
60°-70°	8.4	0.8
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.4	55.9
0°-40°	892.3	82.0
0°-60°	1078.9	99.2
0°-90°	1087.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1087.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	846	
5°	821	78
15°	778	219
25°	681	312
35°	476	284
45°	167	134
55°	56	53
65°	6	8
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583603

CATALOG NUMBER: HC807D010-HM80520835-81WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	846.4
2.5°	835.4
5°	820.6
7.5°	812.1
10°	805.0
12.5°	793.4
15°	777.8
17.5°	758.3
20°	733.7
22.5°	707.9
25°	681.3
27.5°	648.9
30°	608.1
32.5°	553.0
35°	476.0
37.5°	367.8
40°	268.8
42.5°	206.6
45°	167.1
47.5°	137.3
50°	109.5
52.5°	82.2
55°	55.7
57.5°	35.0
60°	21.4
62.5°	12.9
65°	6.5
67.5°	3.2
70°	1.9
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)