

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583691

Luminaire Tested: **HC807D010-HM80520940-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC807D010-HM80520940-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1008.0 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583691

CATALOG NUMBER: HC807D010-HM80520940-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P583691

CATALOG NUMBER: HC807D010-HM80520940-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17703
5°	17579
10°	17535
15°	17996
20°	19479
25°	20884
30°	20417
35°	17000
40°	10442
45°	7235
50°	5522
55°	3618
60°	2263
65°	1700
70°	1713
75°	1966
80°	2166
85°	1946



TEST NUMBER: P583691

CATALOG NUMBER: HC807D010-HM80520940-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	5.4
10°-20°	161.8	16.1
20°-30°	278.5	27.6
30°-40°	269.8	26.8
40°-50°	133.0	13.2
50°-60°	62.7	6.2
60°-70°	24.7	2.5
70°-80°	17.1	1.7
80°-90°	6.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	494.3	49.0
0°-40°	764.2	75.8
0°-60°	959.8	95.2
0°-90°	1008.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1008.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	574	
5°	568	54
15°	564	162
25°	614	279
35°	452	270
45°	166	133
55°	67	63
65°	23	25
75°	16	17
85°	6	6
90°	0	



TEST NUMBER: P583691

CATALOG NUMBER: HC807D010-HM80520940-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	574.1
2.5°	572.2
5°	567.9
7.5°	563.7
10°	560.0
12.5°	559.4
15°	563.7
17.5°	576.5
20°	593.6
22.5°	609.0
25°	613.8
27.5°	602.8
30°	573.4
32.5°	525.1
35°	451.6
37.5°	350.6
40°	259.4
42.5°	201.4
45°	165.9
47.5°	139.6
50°	115.1
52.5°	90.6
55°	67.3
57.5°	49.0
60°	36.7
62.5°	28.8
65°	23.3
67.5°	20.2
70°	19.0
72.5°	17.8
75°	16.5
77.5°	14.7
80°	12.2
82.5°	9.2
85°	5.5
87.5°	2.4
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)