

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583678

Luminaire Tested: **HC807D010-HM80520940-81MDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583678  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC807D010-HM80520940-81MDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 988.9 lumens  
Efficiency: N/A  
Efficacy: 123.6 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583678

CATALOG NUMBER: HC807D010-HM80520940-81MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P583678

CATALOG NUMBER: HC807D010-HM80520940-81MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	59089
5°	56377
10°	48675
15°	37217
20°	28477
25°	22527
30°	17020
35°	9057
40°	3450
45°	1657
50°	705
55°	296
60°	111
65°	88
70°	54
75°	0
80°	0
85°	0



TEST NUMBER: P583678

CATALOG NUMBER: HC807D010-HM80520940-81MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.3	16.7
10°-20°	325.5	32.9
20°-30°	303.1	30.7
30°-40°	156.4	15.8
40°-50°	31.9	3.2
50°-60°	5.4	0.6
60°-70°	1.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	793.9	80.3
0°-40°	950.3	96.1
0°-60°	987.7	99.9
0°-90°	988.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	988.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1916	
5°	1821	165
15°	1166	325
25°	662	303
35°	241	156
45°	38	32
55°	6	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P583678

CATALOG NUMBER: HC807D010-HM80520940-81MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1916.2
2.5°	1890.5
5°	1821.3
7.5°	1707.4
10°	1554.5
12.5°	1353.7
15°	1165.8
17.5°	1003.1
20°	867.8
22.5°	757.6
25°	662.1
27.5°	571.6
30°	478.0
32.5°	366.6
35°	240.6
37.5°	139.6
40°	85.7
42.5°	56.3
45°	38.0
47.5°	23.9
50°	14.7
52.5°	8.6
55°	5.5
57.5°	2.4
60°	1.8
62.5°	1.2
65°	1.2
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)