

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579698

Luminaire Tested: **HCC4S10D010MW-HM40525827-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S10D010MW-HM40525827-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1003.3 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579698
CATALOG NUMBER: HCC4S10D010MW-HM40525827-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579698

CATALOG NUMBER: HCC4S10D010MW-HM40525827-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	64917	64917	64917
5°	66638	64930	63716
10°	68135	64365	61835
15°	70054	63465	60209
20°	69857	61024	57768
25°	66919	57133	54997
30°	61557	52613	52057
35°	54148	47763	48155
40°	46856	42750	44521
45°	40714	37975	40260
50°	36133	33504	35769
55°	32063	29397	30666
60°	28542	25483	25483
65°	25363	21189	19876
70°	21927	16048	14173
75°	18396	10580	8721
80°	13922	5114	4617
85°	7359	1840	1840



TEST NUMBER: P579698
 CATALOG NUMBER: HCC4S10D010MW-HM40525827-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.8	5.0
10°-20°	141.3	14.1
20°-30°	199.3	19.9
30°-40°	205.9	20.5
40°-50°	174.5	17.4
50°-60°	127.0	12.7
60°-70°	74.2	7.4
70°-80°	27.6	2.7
80°-90°	3.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	390.5	38.9
0°-40°	596.3	59.4
0°-60°	897.9	89.5
0°-90°	1003.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1003.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	526	526	526	526	526	
5°	538	534	524	516	515	52
15°	549	532	497	476	472	154
25°	492	464	420	405	404	225
35°	360	344	317	318	320	225
45°	233	227	218	226	231	182
55°	149	142	137	141	143	134
65°	87	80	73	68	68	86
75°	39	32	22	18	18	41
85°	5	3	1	1	1	7
90°	0	0	0	0	0	



TEST NUMBER: P579698

CATALOG NUMBER: HCC4S10D010MW-HM40525827-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	526.3	526.3	526.3	526.3	526.3	526.3	526.3	526.3	526.3
2.5°	530.9	529.6	528.3	526.3	523.7	521.8	519.8	518.5	518.5
5°	538.2	536.1	533.5	528.9	524.4	520.5	516.5	514.6	514.6
7.5°	543.4	540.8	535.5	528.9	521.1	515.3	509.4	506.8	505.4
10°	544.0	541.3	534.2	524.4	513.9	504.8	498.2	494.3	493.7
12.5°	545.3	542.0	532.9	519.2	505.4	494.3	487.1	483.2	481.9
15°	548.6	544.0	531.6	513.9	497.0	483.9	476.0	472.7	471.5
17.5°	545.3	538.7	523.7	502.8	483.9	469.4	461.6	458.4	458.4
20°	532.2	525.6	508.0	485.1	464.9	451.1	443.4	441.3	440.1
22.5°	513.9	506.8	487.7	463.6	443.4	430.8	425.6	423.0	422.4
25°	491.7	484.6	464.2	439.4	419.8	409.3	404.8	404.8	404.1
27.5°	466.8	457.7	436.8	415.1	396.3	388.4	386.5	386.5	387.0
30°	432.2	425.6	408.0	387.0	369.4	364.2	364.2	365.5	365.5
32.5°	394.9	390.3	374.6	356.3	342.7	339.4	340.6	343.2	343.9
35°	359.6	354.4	343.9	327.6	317.2	315.8	317.7	319.8	319.8
37.5°	325.0	319.8	312.5	299.5	291.7	292.2	294.9	297.5	299.5
40°	291.0	287.0	281.8	271.3	265.5	268.1	271.3	273.9	276.5
42.5°	260.9	257.0	253.1	245.2	241.3	244.6	248.4	251.0	253.7
45°	233.4	230.8	226.9	220.3	217.7	221.0	225.6	228.2	230.8
47.5°	209.8	208.6	203.4	197.4	196.2	199.4	203.4	206.7	208.6
50°	188.3	186.4	181.7	175.9	174.6	179.8	182.4	184.4	186.4
52.5°	167.4	165.5	160.2	155.0	155.0	158.9	160.8	161.5	163.4
55°	149.1	147.1	141.9	137.9	136.7	140.0	141.2	141.2	142.6
57.5°	132.1	130.1	124.8	120.3	119.6	121.7	121.7	121.7	122.2
60°	115.7	113.8	108.6	104.6	103.3	104.0	103.3	102.6	103.3
62.5°	100.7	98.8	93.5	88.9	87.6	87.6	85.7	85.0	85.7
65°	86.9	83.6	79.8	75.2	72.6	70.7	68.1	68.1	68.1
67.5°	73.3	70.7	66.0	61.5	58.2	55.0	51.0	52.3	52.9
70°	60.8	58.8	53.6	49.0	44.5	40.5	37.3	38.6	39.3
72.5°	49.7	47.1	42.4	37.3	33.3	28.1	26.2	27.4	27.4
75°	38.6	36.0	32.1	26.9	22.2	17.6	17.6	18.3	18.3
77.5°	28.8	26.2	22.2	17.6	13.8	10.5	11.2	11.2	11.2
80°	19.6	17.6	14.3	10.5	7.2	5.9	5.9	5.9	6.5
82.5°	11.2	9.8	7.9	5.2	3.3	3.3	3.3	3.3	3.3
85°	5.2	3.9	3.3	1.9	1.3	1.3	1.3	1.3	1.3
87.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)