

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585197

Luminaire Tested: **HC880D010-HM86080827-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585197  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC880D010-HM86080827-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6996.7 lumens  
Efficiency: N/A  
Efficacy: 100.0 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585197

CATALOG NUMBER: HC880D010-HM86080827-81WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P585197

CATALOG NUMBER: HC880D010-HM86080827-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	167864
5°	163348
10°	162105
15°	159691
20°	154855
25°	149080
30°	139258
35°	115240
40°	69575
45°	46862
50°	33768
55°	19257
60°	8474
65°	3035
70°	1127
75°	500
80°	0
85°	0



TEST NUMBER: P585197

CATALOG NUMBER: HC880D010-HM86080827-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	501.3	7.2
10°-20°	1405.8	20.1
20°-30°	2005.4	28.7
30°-40°	1826.1	26.1
40°-50°	861.4	12.3
50°-60°	338.8	4.8
60°-70°	54.0	0.8
70°-80°	3.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3912.5	55.9
0°-40°	5738.6	82.0
0°-60°	6938.9	99.2
0°-90°	6996.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6996.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5444	
5°	5277	501
15°	5002	1406
25°	4382	2005
35°	3061	1826
45°	1075	861
55°	358	339
65°	42	54
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P585197

CATALOG NUMBER: HC880D010-HM86080827-81WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5443.7
2.5°	5373.0
5°	5277.1
7.5°	5222.9
10°	5177.1
12.5°	5102.2
15°	5002.2
17.5°	4877.3
20°	4719.0
22.5°	4552.4
25°	4381.6
27.5°	4173.4
30°	3911.0
32.5°	3556.9
35°	3061.3
37.5°	2365.8
40°	1728.4
42.5°	1328.7
45°	1074.6
47.5°	883.0
50°	703.9
52.5°	529.0
55°	358.2
57.5°	225.0
60°	137.4
62.5°	83.3
65°	41.6
67.5°	20.8
70°	12.5
72.5°	4.2
75°	4.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)