

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585222

Luminaire Tested: **HC880D010-HM86080835-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585222
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC880D010-HM86080835-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7344.7 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585222

CATALOG NUMBER: HC880D010-HM86080835-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P585222

CATALOG NUMBER: HC880D010-HM86080835-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	335891
5°	306087
10°	261524
15°	228069
20°	203278
25°	180318
30°	147636
35°	84778
40°	37625
45°	21896
50°	12641
55°	7215
60°	3990
65°	2539
70°	1794
75°	1191
80°	888
85°	1769



TEST NUMBER: P585222

CATALOG NUMBER: HC880D010-HM86080835-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	895.1	12.2
10°-20°	2008.2	27.3
20°-30°	2403.8	32.7
30°-40°	1454.2	19.8
40°-50°	407.5	5.5
50°-60°	126.6	1.7
60°-70°	36.1	0.5
70°-80°	9.9	0.1
80°-90°	3.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5307.0	72.3
0°-40°	6761.2	92.1
0°-60°	7295.3	99.3
0°-90°	7344.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7344.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10893	
5°	9888	895
15°	7144	2008
25°	5300	2404
35°	2252	1454
45°	502	408
55°	134	127
65°	35	36
75°	10	10
85°	5	3
90°	0	



TEST NUMBER: P585222

CATALOG NUMBER: HC880D010-HM86080835-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10892.7
2.5°	10584.5
5°	9888.4
7.5°	9103.0
10°	8352.2
12.5°	7695.9
15°	7144.1
17.5°	6657.0
20°	6194.6
22.5°	5767.0
25°	5299.7
27.5°	4772.6
30°	4146.3
32.5°	3336.0
35°	2252.1
37.5°	1401.9
40°	934.7
42.5°	671.2
45°	502.1
47.5°	367.9
50°	263.5
52.5°	183.9
55°	134.2
57.5°	89.5
60°	64.7
62.5°	44.7
65°	34.8
67.5°	24.9
70°	19.9
72.5°	10.0
75°	10.0
77.5°	5.0
80°	5.0
82.5°	5.0
85°	5.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)