

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579714

Luminaire Tested: **HCC4W10D010MB-HM40525830-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010MB-HM40525830-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1055.4 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579714
CATALOG NUMBER: HCC4W10D010MB-HM40525830-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P579714

CATALOG NUMBER: HCC4W10D010MB-HM40525830-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	84381	84381	84381
5°	84171	84257	84257
10°	83203	83278	83203
15°	82211	82211	82211
20°	78823	79006	79111
25°	73724	73833	74023
30°	66058	66257	66257
35°	53636	54057	54163
40°	40479	40721	40818
45°	31015	30893	30893
50°	25541	25426	25426
55°	21935	21784	21784
60°	19563	19390	19390
65°	18387	18387	18387
70°	17130	17130	17130
75°	15489	15822	15489
80°	14562	14064	14562
85°	12029	12029	12029



TEST NUMBER: P579714
 CATALOG NUMBER: HCC4W10D010MB-HM40525830-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.5	6.1
10°-20°	180.4	17.1
20°-30°	247.9	23.5
30°-40°	222.8	21.1
40°-50°	140.8	13.3
50°-60°	92.0	8.7
60°-70°	62.3	5.9
70°-80°	35.0	3.3
80°-90°	9.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.7	46.7
0°-40°	715.5	67.8
0°-60°	948.3	89.9
0°-90°	1055.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1055.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	684	684	684	684	684	
5°	680	680	680	680	680	64
15°	644	644	644	644	644	180
25°	542	542	542	544	544	247
35°	356	358	359	360	360	222
45°	178	177	177	177	177	141
55°	102	102	101	102	101	92
65°	63	63	63	63	63	62
75°	32	33	33	33	32	35
85°	8	8	8	8	8	10
90°	0	0	0	0	0	



TEST NUMBER: P579714

CATALOG NUMBER: HCC4W10D010MB-HM40525830-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	684.1	684.1	684.1	684.1	684.1
2.5°	680.5	680.5	680.5	680.5	680.5
5°	679.8	679.8	680.5	680.5	680.5
7.5°	674.8	675.6	675.6	675.6	675.6
10°	664.3	664.3	664.9	664.9	664.3
12.5°	654.3	654.3	654.3	655.0	654.3
15°	643.8	643.8	643.8	643.8	643.8
17.5°	625.3	626.0	626.0	626.0	626.0
20°	600.5	601.9	601.9	602.7	602.7
22.5°	572.2	572.9	573.6	574.3	573.6
25°	541.7	542.5	542.5	543.9	543.9
27.5°	506.3	507.1	508.5	508.5	508.5
30°	463.8	464.5	465.2	465.2	465.2
32.5°	413.5	413.5	415.0	415.7	415.0
35°	356.2	357.7	359.0	360.4	359.7
37.5°	301.7	303.0	303.8	303.8	304.5
40°	251.4	252.9	252.9	254.2	253.5
42.5°	211.8	211.0	211.0	212.5	211.8
45°	177.8	177.1	177.1	177.1	177.1
47.5°	152.9	152.3	152.3	152.3	152.3
50°	133.1	132.5	132.5	132.5	132.5
52.5°	116.9	116.2	116.2	116.2	115.4
55°	102.0	102.0	101.3	102.0	101.3
57.5°	88.5	88.5	88.5	88.5	88.5
60°	79.3	78.6	78.6	78.6	78.6
62.5°	70.8	70.8	70.8	70.8	70.8
65°	63.0	63.0	63.0	63.0	63.0
67.5°	55.2	54.5	55.2	55.2	54.5
70°	47.5	46.8	47.5	47.5	47.5
72.5°	39.6	39.6	39.6	40.4	39.6
75°	32.5	33.2	33.2	33.2	32.5
77.5°	26.2	26.9	26.2	26.2	26.2
80°	20.5	19.8	19.8	19.8	20.5
82.5°	14.1	14.1	14.1	14.1	14.1
85°	8.5	8.5	8.5	8.5	8.5
87.5°	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)