

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593894

Luminaire Tested: **HC880D010-HM86080850-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593894
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC880D010-HM86080850-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8285.3 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593894

CATALOG NUMBER: HC880D010-HM86080850-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P593894

CATALOG NUMBER: HC880D010-HM86080850-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	189683
5°	185409
10°	179725
15°	176090
20°	174509
25°	171900
30°	162833
35°	135289
40°	79671
45°	52697
50°	41477
55°	30520
60°	21197
65°	12915
70°	5635
75°	2478
80°	1865
85°	0



TEST NUMBER: P593894

CATALOG NUMBER: HC880D010-HM86080850-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	564.1	6.8
10°-20°	1559.4	18.8
20°-30°	2310.4	27.9
30°-40°	2134.9	25.8
40°-50°	984.4	11.9
50°-60°	517.7	6.2
60°-70°	182.9	2.2
70°-80°	28.7	0.3
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4433.8	53.5
0°-40°	6568.7	79.3
0°-60°	8070.8	97.4
0°-90°	8285.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8285.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6151	
5°	5990	564
15°	5516	1559
25°	5052	2310
35°	3594	2135
45°	1208	984
55°	568	518
65°	177	183
75°	21	29
85°	0	3
90°	0	



TEST NUMBER: P593894

CATALOG NUMBER: HC880D010-HM86080850-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6151.3
2.5°	6099.2
5°	5989.8
7.5°	5870.1
10°	5739.8
12.5°	5614.8
15°	5515.9
17.5°	5427.3
20°	5317.9
22.5°	5198.2
25°	5052.3
27.5°	4854.3
30°	4573.1
32.5°	4172.1
35°	3593.9
37.5°	2760.5
40°	1979.2
42.5°	1484.5
45°	1208.4
47.5°	1026.1
50°	864.6
52.5°	708.4
55°	567.7
57.5°	447.9
60°	343.7
62.5°	260.4
65°	177.0
67.5°	104.2
70°	62.5
72.5°	36.5
75°	20.8
77.5°	15.6
80°	10.5
82.5°	5.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)