

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585256

Luminaire Tested: **HC880D010-HM86080927-81MDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585256  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC880D010-HM86080927-81MDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5357.8 lumens  
Efficiency: N/A  
Efficacy: 76.5 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585256

CATALOG NUMBER: HC880D010-HM86080927-81MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P585256

CATALOG NUMBER: HC880D010-HM86080927-81MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	245013
5°	223275
10°	190772
15°	166366
20°	148283
25°	131530
30°	107692
35°	61842
40°	27445
45°	15974
50°	9225
55°	5269
60°	2911
65°	1853
70°	1307
75°	870
80°	657
85°	1309



TEST NUMBER: P585256

CATALOG NUMBER: HC880D010-HM86080927-81MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	652.9	12.2
10°-20°	1464.9	27.3
20°-30°	1753.4	32.7
30°-40°	1060.8	19.8
40°-50°	297.3	5.5
50°-60°	92.4	1.7
60°-70°	26.4	0.5
70°-80°	7.2	0.1
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3871.2	72.3
0°-40°	4932.0	92.1
0°-60°	5321.7	99.3
0°-90°	5357.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5357.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7946	
5°	7213	653
15°	5211	1465
25°	3866	1753
35°	1643	1061
45°	366	297
55°	98	92
65°	25	26
75°	7	7
85°	4	3
90°	0	



TEST NUMBER: P585256

CATALOG NUMBER: HC880D010-HM86080927-81MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7945.6
2.5°	7720.8
5°	7213.1
7.5°	6640.1
10°	6092.6
12.5°	5613.9
15°	5211.3
17.5°	4855.9
20°	4518.7
22.5°	4206.8
25°	3865.8
27.5°	3481.4
30°	3024.5
32.5°	2433.4
35°	1642.8
37.5°	1022.7
40°	681.8
42.5°	489.6
45°	366.3
47.5°	268.4
50°	192.3
52.5°	134.2
55°	98.0
57.5°	65.3
60°	47.2
62.5°	32.7
65°	25.4
67.5°	18.2
70°	14.5
72.5°	7.3
75°	7.3
77.5°	3.7
80°	3.7
82.5°	3.7
85°	3.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)