

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579731

Luminaire Tested: **HCC4S10D010BZ-HM40525835-41PSMDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579731  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S10D010BZ-HM40525835-41PSMDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1038.1 lumens  
Efficiency: N/A  
Efficacy: 104.9 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579731  
CATALOG NUMBER: HCC4S10D010BZ-HM40525835-41PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P579731

CATALOG NUMBER: HCC4S10D010BZ-HM40525835-41PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78																			
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70																			
4	90	80	73	68	88	79	72	67	77	71	66	74	69	65	72	68	65	63																			
5	84	74	66	61	82	72	66	60	71	64	60	69	63	59	67	62	59	57																			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52																			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47																			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44																			
9	66	54	47	42	65	54	47	42	53	47	42	52	46	42	51	46	42	40																			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	90190
5°	89619
10°	87711
15°	85761
20°	81802
25°	75724
30°	65873
35°	49751
40°	36035
45°	28172
50°	24082
55°	20817
60°	19193
65°	17570
70°	16409
75°	15012
80°	14064
85°	13586



TEST NUMBER: P579731  
 CATALOG NUMBER: HCC4S10D010BZ-HM40525835-41PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.4	6.6
10°-20°	188.1	18.1
20°-30°	253.0	24.4
30°-40°	208.0	20.0
40°-50°	127.8	12.3
50°-60°	88.4	8.5
60°-70°	60.3	5.8
70°-80°	33.5	3.2
80°-90°	10.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	509.5	49.1
0°-40°	717.5	69.1
0°-60°	933.7	89.9
0°-90°	1038.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1038.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	731	
5°	724	68
15°	672	188
25°	556	253
35°	330	208
45°	162	128
55°	97	88
65°	60	60
75°	32	34
85°	10	11
90°	0	



TEST NUMBER: P579731  
CATALOG NUMBER: HCC4S10D010BZ-HM40525835-41PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	731.2
2.5°	725.9
5°	723.8
7.5°	715.7
10°	700.3
12.5°	686.3
15°	671.6
17.5°	650.4
20°	623.2
22.5°	591.0
25°	556.4
27.5°	514.6
30°	462.5
32.5°	398.6
35°	330.4
37.5°	271.6
40°	223.8
42.5°	187.2
45°	161.5
47.5°	141.7
50°	125.5
52.5°	110.8
55°	96.8
57.5°	86.6
60°	77.8
62.5°	69.0
65°	60.2
67.5°	52.8
70°	45.5
72.5°	38.1
75°	31.5
77.5°	24.9
80°	19.8
82.5°	14.7
85°	9.6
87.5°	5.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)