

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585257

Luminaire Tested: **HC880D010-HM86080927-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC880D010-HM86080927-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5372.0 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 70
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585257

CATALOG NUMBER: HC880D010-HM86080927-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P585257

CATALOG NUMBER: HC880D010-HM86080927-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80	80	80	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72	72	72	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65	65	65	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59	59	59	59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54	54	54	54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50	50	50	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46	46	46	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43	43	43	43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40	40	40	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	137363
5°	133623
10°	125740
15°	119048
20°	114516
25°	110092
30°	97776
35°	62267
40°	34751
45°	29109
50°	26279
55°	24768
60°	22591
65°	20379
70°	17987
75°	15989
80°	14171
85°	12843



TEST NUMBER: P585257

CATALOG NUMBER: HC880D010-HM86080927-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	402.4	7.5
10°-20°	1051.7	19.6
20°-30°	1467.2	27.3
30°-40°	1055.7	19.7
40°-50°	523.2	9.7
50°-60°	409.3	7.6
60°-70°	277.1	5.2
70°-80°	143.9	2.7
80°-90°	41.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2921.3	54.4
0°-40°	3977.0	74.0
0°-60°	4909.5	91.4
0°-90°	5372.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5372.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4455	
5°	4317	402
15°	3729	1052
25°	3236	1467
35°	1654	1056
45°	668	523
55°	461	409
65°	279	277
75°	134	144
85°	36	41
90°	0	



TEST NUMBER: P585257

CATALOG NUMBER: HC880D010-HM86080927-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4454.6
2.5°	4414.8
5°	4316.8
7.5°	4178.9
10°	4015.7
12.5°	3863.3
15°	3729.1
17.5°	3602.2
20°	3489.7
22.5°	3377.2
25°	3235.7
27.5°	3032.7
30°	2746.0
32.5°	2296.2
35°	1654.1
37.5°	1128.1
40°	863.3
42.5°	743.6
45°	667.5
47.5°	602.2
50°	547.8
52.5°	500.6
55°	460.7
57.5°	413.5
60°	366.3
62.5°	319.2
65°	279.3
67.5°	239.5
70°	199.5
72.5°	166.8
75°	134.2
77.5°	105.2
80°	79.8
82.5°	58.0
85°	36.3
87.5°	18.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)