

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585260

Luminaire Tested: **HC880D010-HM86080927-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585260
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC880D010-HM86080927-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4857.0 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 70
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585260

CATALOG NUMBER: HC880D010-HM86080927-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P585260

CATALOG NUMBER: HC880D010-HM86080927-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81																			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73																			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61																			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56																			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52																			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45																			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121063
5°	120740
10°	118726
15°	116992
20°	114187
25°	108394
30°	89405
35°	46031
40°	30818
45°	26423
50°	22806
55°	19897
60°	17682
65°	15884
70°	14398
75°	12975
80°	11596
85°	11569



TEST NUMBER: P585260

CATALOG NUMBER: HC880D010-HM86080927-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	368.8	7.6
10°-20°	1031.1	21.2
20°-30°	1428.6	29.4
30°-40°	858.1	17.7
40°-50°	469.8	9.7
50°-60°	333.7	6.9
60°-70°	216.6	4.5
70°-80°	115.8	2.4
80°-90°	34.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2828.5	58.2
0°-40°	3686.6	75.9
0°-60°	4490.0	92.4
0°-90°	4857.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4857.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3926	
5°	3901	369
15°	3665	1031
25°	3186	1429
35°	1223	858
45°	606	470
55°	370	334
65°	218	217
75°	109	116
85°	33	35
90°	0	



TEST NUMBER: P585260

CATALOG NUMBER: HC880D010-HM86080927-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3926.0
2.5°	3918.7
5°	3900.6
7.5°	3857.1
10°	3791.7
12.5°	3730.0
15°	3664.7
17.5°	3581.3
20°	3479.7
22.5°	3356.3
25°	3185.8
27.5°	2917.3
30°	2510.9
32.5°	1839.6
35°	1222.8
37.5°	903.5
40°	765.6
42.5°	678.6
45°	605.9
47.5°	537.1
50°	475.4
52.5°	417.2
55°	370.1
57.5°	326.6
60°	286.7
62.5°	250.4
65°	217.7
67.5°	185.0
70°	159.7
72.5°	130.7
75°	108.9
77.5°	87.0
80°	65.3
82.5°	47.2
85°	32.7
87.5°	14.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)