

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585290

Luminaire Tested: **HC880D010-HM86080935-81MDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585290  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC880D010-HM86080935-81MDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6517.0 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585290

CATALOG NUMBER: HC880D010-HM86080935-81MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P585290

CATALOG NUMBER: HC880D010-HM86080935-81MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	298036
5°	271594
10°	232053
15°	202367
20°	180369
25°	159998
30°	130997
35°	75228
40°	33383
45°	19428
50°	11216
55°	6403
60°	3534
65°	2255
70°	1587
75°	1048
80°	781
85°	1557



TEST NUMBER: P585290

CATALOG NUMBER: HC880D010-HM86080935-81MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	794.2	12.2
10°-20°	1781.9	27.3
20°-30°	2132.9	32.7
30°-40°	1290.3	19.8
40°-50°	361.6	5.5
50°-60°	112.3	1.7
60°-70°	32.1	0.5
70°-80°	8.7	0.1
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4709.0	72.3
0°-40°	5999.3	92.1
0°-60°	6473.2	99.3
0°-90°	6517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6517.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9665	
5°	8774	794
15°	6339	1782
25°	4702	2133
35°	1998	1290
45°	446	362
55°	119	112
65°	31	32
75°	9	9
85°	4	3
90°	0	



TEST NUMBER: P585290

CATALOG NUMBER: HC880D010-HM86080935-81MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9665.1
2.5°	9391.7
5°	8774.1
7.5°	8077.1
10°	7411.0
12.5°	6828.7
15°	6339.0
17.5°	5906.7
20°	5496.5
22.5°	5117.1
25°	4702.5
27.5°	4234.9
30°	3679.0
32.5°	2960.0
35°	1998.4
37.5°	1244.1
40°	829.3
42.5°	595.6
45°	445.5
47.5°	326.4
50°	233.8
52.5°	163.2
55°	119.1
57.5°	79.4
60°	57.3
62.5°	39.7
65°	30.9
67.5°	22.1
70°	17.6
72.5°	8.8
75°	8.8
77.5°	4.4
80°	4.4
82.5°	4.4
85°	4.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)