

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579687

Luminaire Tested: **HCC4W10D010MB-HM40525827-41NDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579687  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W10D010MB-HM40525827-41NDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 907.7 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579687  
CATALOG NUMBER: HCC4W10D010MB-HM40525827-41NDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579687

CATALOG NUMBER: HCC4W10D010MB-HM40525827-41NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63				63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54				54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51				51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48				48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117746
5°	115595
10°	109655
15°	102528
20°	93104
25°	82393
30°	68522
35°	49419
40°	30835
45°	17793
50°	10036
55°	4774
60°	2763
65°	2101
70°	1406
75°	905
80°	923
85°	991



TEST NUMBER: P579687  
 CATALOG NUMBER: HCC4W10D010MB-HM40525827-41NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.3	9.6
10°-20°	224.0	24.7
20°-30°	275.5	30.3
30°-40°	204.6	22.5
40°-50°	83.2	9.2
50°-60°	23.0	2.5
60°-70°	7.2	0.8
70°-80°	2.4	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	586.7	64.6
0°-40°	791.3	87.2
0°-60°	897.4	98.9
0°-90°	907.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	907.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	955	
5°	934	87
15°	803	224
25°	605	275
35°	328	205
45°	102	83
55°	22	23
65°	7	7
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P579687  
CATALOG NUMBER: HCC4W10D010MB-HM40525827-41NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	954.6
2.5°	945.3
5°	933.6
7.5°	910.1
10°	875.5
12.5°	839.5
15°	802.9
17.5°	759.0
20°	709.3
22.5°	659.0
25°	605.4
27.5°	547.3
30°	481.1
32.5°	406.0
35°	328.2
37.5°	255.0
40°	191.5
42.5°	139.9
45°	102.0
47.5°	73.2
50°	52.3
52.5°	36.0
55°	22.2
57.5°	14.3
60°	11.2
62.5°	9.1
65°	7.2
67.5°	5.2
70°	3.9
72.5°	3.3
75°	1.9
77.5°	1.3
80°	1.3
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)