

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579702

Luminaire Tested: **HCC4W10D010BZ-HM40525830-41WDBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579702  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W10D010BZ-HM40525830-41WDBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 918.7 lumens  
Efficiency: N/A  
Efficacy: 92.8 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579702  
CATALOG NUMBER: HCC4W10D010BZ-HM40525830-41WDBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579702

CATALOG NUMBER: HCC4W10D010BZ-HM40525830-41WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93																												
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																												
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78																												
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72																												
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																												
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																												
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																												
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52																												
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49																												
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	91633
5°	91711
10°	91895
15°	93219
20°	90912
25°	85292
30°	75444
35°	57370
40°	36148
45°	20741
50°	11015
55°	4580
60°	1233
65°	1022
70°	793
75°	667
80°	497
85°	991



TEST NUMBER: P579702  
 CATALOG NUMBER: HCC4W10D010BZ-HM40525830-41WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.4	7.7
10°-20°	204.4	22.3
20°-30°	285.3	31.1
30°-40°	234.8	25.6
40°-50°	96.7	10.5
50°-60°	21.8	2.4
60°-70°	3.5	0.4
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.2	61.0
0°-40°	795.0	86.5
0°-60°	913.5	99.4
0°-90°	918.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	918.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	743	
5°	741	70
15°	730	204
25°	627	285
35°	381	235
45°	119	97
55°	21	22
65°	4	3
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P579702  
CATALOG NUMBER: HCC4W10D010BZ-HM40525830-41WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	742.9
2.5°	739.2
5°	740.7
7.5°	737.9
10°	733.7
12.5°	731.5
15°	730.0
17.5°	717.3
20°	692.6
22.5°	661.4
25°	626.7
27.5°	584.9
30°	529.7
32.5°	461.7
35°	381.0
37.5°	299.5
40°	224.5
42.5°	163.5
45°	118.9
47.5°	85.0
50°	57.4
52.5°	36.1
55°	21.3
57.5°	10.6
60°	5.0
62.5°	4.2
65°	3.5
67.5°	2.8
70°	2.2
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)