

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579711

Luminaire Tested: **HCC4S10D010SL-HM40525830-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S10D010SL-HM40525830-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1022.8 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579711
CATALOG NUMBER: HCC4S10D010SL-HM40525830-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P579711
 CATALOG NUMBER: HCC4S10D010SL-HM40525830-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																											
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79																											
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70																											
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63																											
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57																											
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52																											
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47																											
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44																											
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40																											
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86724
5°	86263
10°	84680
15°	82901
20°	79348
25°	73778
30°	65303
35°	51543
40°	38563
45°	29672
50°	24063
55°	19978
60°	17663
65°	16344
70°	15075
75°	13821
80°	12644
85°	10048

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P579711

CATALOG NUMBER: HCC4S10D010SL-HM40525830-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	6.4
10°-20°	182.1	17.8
20°-30°	247.2	24.2
30°-40°	214.1	20.9
40°-50°	134.4	13.1
50°-60°	84.6	8.3
60°-70°	55.5	5.4
70°-80°	30.6	3.0
80°-90°	8.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	495.1	48.4
0°-40°	709.2	69.3
0°-60°	928.3	90.8
0°-90°	1022.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1022.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	703	
5°	697	66
15°	649	182
25°	542	247
35°	342	214
45°	170	134
55°	93	85
65°	56	56
75°	29	31
85°	7	8
90°	0	



TEST NUMBER: P579711
CATALOG NUMBER: HCC4S10D010SL-HM40525830-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	703.1
2.5°	698.8
5°	696.7
7.5°	689.6
10°	676.1
12.5°	662.7
15°	649.2
17.5°	630.8
20°	604.5
22.5°	574.8
25°	542.1
27.5°	504.6
30°	458.5
32.5°	402.5
35°	342.3
37.5°	287.0
40°	239.5
42.5°	202.0
45°	170.1
47.5°	146.0
50°	125.4
52.5°	107.8
55°	92.9
57.5°	80.1
60°	71.6
62.5°	63.8
65°	56.0
67.5°	48.1
70°	41.8
72.5°	34.7
75°	29.0
77.5°	22.6
80°	17.8
82.5°	12.1
85°	7.1
87.5°	2.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)