

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579805

Luminaire Tested: **HCC4S10D010MB-HM40525935-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S10D010MB-HM40525935-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1011.2 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579805
CATALOG NUMBER: HCC4S10D010MB-HM40525935-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P579805

CATALOG NUMBER: HCC4S10D010MB-HM40525935-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	59847	59847	59847
5°	62267	60410	59754
10°	64315	60933	59618
15°	66568	61116	59609
20°	66786	59645	58871
25°	64428	56671	57120
30°	59948	52755	54265
35°	54012	48290	50052
40°	47629	43925	45922
45°	41621	39580	41533
50°	36862	35615	37496
55°	32429	31440	32730
60°	28937	26840	27654
65°	25450	21831	21423
70°	22251	16084	14642
75°	18443	9722	7816
80°	13993	3694	2344
85°	6510	991	991



TEST NUMBER: P579805
 CATALOG NUMBER: HCC4S10D010MB-HM40525935-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	4.6
10°-20°	136.6	13.5
20°-30°	197.8	19.6
30°-40°	208.7	20.6
40°-50°	180.6	17.9
50°-60°	133.8	13.2
60°-70°	77.1	7.6
70°-80°	26.9	2.7
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.2	37.7
0°-40°	589.9	58.3
0°-60°	904.3	89.4
0°-90°	1011.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1011.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	485	485	485	485	485	
5°	503	496	488	484	483	48
15°	521	504	479	468	467	147
25°	473	450	416	414	420	217
35°	359	342	321	328	332	224
45°	239	232	227	236	238	185
55°	151	148	146	152	152	136
65°	87	82	75	71	73	87
75°	39	33	20	16	16	42
85°	5	3	1	1	1	7
90°	0	0	0	0	0	



TEST NUMBER: P579805

CATALOG NUMBER: HCC4S10D010MB-HM40525935-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	485.2	485.2	485.2	485.2	485.2	485.2	485.2	485.2	485.2
2.5°	492.4	491.2	489.1	486.5	483.9	481.9	481.3	480.6	480.6
5°	502.9	500.3	496.4	491.2	487.9	485.9	483.9	482.6	482.6
7.5°	510.2	507.5	501.6	494.3	489.8	485.9	483.3	481.3	481.3
10°	513.5	510.2	502.9	493.8	486.5	481.3	477.4	476.0	476.0
12.5°	517.3	513.5	503.6	491.7	482.6	476.0	472.2	470.8	470.8
15°	521.3	516.7	504.2	490.5	478.6	470.8	467.5	466.8	466.8
17.5°	519.3	513.5	499.0	482.6	469.5	461.6	458.4	458.4	459.0
20°	508.8	502.9	486.5	468.2	454.4	448.5	445.9	447.2	448.5
22.5°	493.1	485.9	468.2	450.4	436.1	430.8	430.8	432.8	434.7
25°	473.4	466.8	449.9	430.2	416.4	412.4	413.8	417.1	419.7
27.5°	451.1	443.9	426.2	407.9	394.1	392.2	395.3	400.0	401.3
30°	420.9	415.0	400.0	382.3	370.4	369.8	374.4	377.7	381.0
32.5°	392.2	385.6	371.1	354.0	345.6	346.2	351.4	355.4	357.3
35°	358.7	352.8	342.3	328.5	320.7	321.9	327.9	331.8	332.4
37.5°	327.2	323.3	312.7	302.3	296.3	299.0	304.3	308.9	308.9
40°	295.8	292.5	284.6	276.1	272.8	276.1	281.3	285.2	285.2
42.5°	265.6	263.6	257.1	251.2	249.2	253.8	258.3	261.6	260.9
45°	238.6	236.7	232.2	227.5	226.9	231.5	235.5	237.4	238.1
47.5°	214.4	213.1	209.2	205.9	205.9	210.5	213.7	215.8	216.3
50°	192.1	190.8	187.5	184.9	185.6	190.2	192.8	194.7	195.4
52.5°	169.8	169.2	166.6	163.3	165.2	168.5	171.8	173.1	173.8
55°	150.8	150.8	147.5	144.9	146.2	149.5	151.5	152.2	152.2
57.5°	133.7	133.1	129.2	126.5	127.2	130.5	131.8	132.5	132.5
60°	117.3	116.8	112.8	108.8	108.8	110.8	111.5	112.1	112.1
62.5°	101.6	100.9	96.4	93.1	91.8	91.2	91.2	92.4	95.0
65°	87.2	86.6	81.9	76.7	74.8	72.8	70.8	72.1	73.4
67.5°	74.1	72.8	68.2	63.6	59.1	55.8	52.5	54.4	57.0
70°	61.7	60.3	55.1	49.8	44.6	39.4	36.8	39.4	40.6
72.5°	49.8	48.5	43.2	38.0	31.5	26.2	25.6	26.2	26.9
75°	38.7	38.0	32.8	26.9	20.4	16.4	16.4	16.4	16.4
77.5°	28.9	27.5	22.3	17.1	11.8	9.2	8.5	8.5	8.5
80°	19.7	18.3	13.8	9.8	5.2	4.0	4.0	3.3	3.3
82.5°	11.2	10.5	7.2	4.0	1.9	1.4	1.4	1.4	1.4
85°	4.6	4.0	2.6	1.4	0.7	0.7	0.7	0.7	0.7
87.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)