

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579806

Luminaire Tested: **HCC4S10D010SL-HM40525935-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S10D010SL-HM40525935-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1005.9 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579806
CATALOG NUMBER: HCC4S10D010SL-HM40525935-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579806

CATALOG NUMBER: HCC4S10D010SL-HM40525935-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	65089	65089	65089
5°	66799	65103	63889
10°	68310	64541	61985
15°	70233	63619	60362
20°	70041	61181	57913
25°	67096	57270	55133
30°	61728	52755	52185
35°	54283	47884	48275
40°	46985	42863	44650
45°	40836	38080	40382
50°	36229	33581	35865
55°	32128	29461	30730
60°	28641	25557	25557
65°	25450	21218	19905
70°	21999	16084	14209
75°	18443	10628	8721
80°	13993	5114	4688
85°	7359	1981	1981



TEST NUMBER: P579806

CATALOG NUMBER: HCC4S10D010SL-HM40525935-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	5.0
10°-20°	141.7	14.1
20°-30°	199.8	19.9
30°-40°	206.4	20.5
40°-50°	175.0	17.4
50°-60°	127.3	12.7
60°-70°	74.4	7.4
70°-80°	27.7	2.7
80°-90°	3.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	391.5	38.9
0°-40°	597.9	59.4
0°-60°	900.2	89.5
0°-90°	1005.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1005.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	528	528	528	528	528	
5°	540	535	526	518	516	52
15°	550	533	498	477	473	155
25°	493	465	421	406	405	225
35°	360	345	318	319	321	225
45°	234	228	218	226	232	182
55°	149	142	137	142	143	134
65°	87	80	73	68	68	87
75°	39	32	22	18	18	42
85°	5	3	1	1	1	7
90°	0	0	0	0	0	



TEST NUMBER: P579806

CATALOG NUMBER: HCC4S10D010SL-HM40525935-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	527.7	527.7	527.7	527.7	527.7	527.7	527.7	527.7	527.7
2.5°	532.4	531.0	529.7	527.7	525.1	523.1	521.2	519.8	519.8
5°	539.5	537.6	535.0	530.3	525.8	521.9	517.9	516.0	516.0
7.5°	544.8	542.1	536.9	530.3	522.5	516.7	510.7	508.1	506.8
10°	545.4	542.8	535.7	525.8	515.3	506.1	499.6	495.6	494.9
12.5°	546.8	543.5	534.3	520.5	506.8	495.6	488.4	484.4	483.2
15°	550.0	545.4	533.0	515.3	498.2	485.1	477.3	474.0	472.7
17.5°	546.8	540.2	525.1	504.1	485.1	470.7	462.8	459.5	459.5
20°	533.6	527.1	509.4	486.5	466.1	452.4	444.5	442.6	441.2
22.5°	515.3	508.1	489.1	464.8	444.5	432.0	426.7	424.1	423.4
25°	493.0	485.8	465.4	440.5	420.8	410.4	405.8	405.8	405.1
27.5°	468.1	459.0	437.9	416.3	397.3	389.4	387.5	387.5	388.1
30°	433.4	426.7	409.1	388.1	370.4	365.2	365.2	366.4	366.4
32.5°	396.0	391.4	375.7	357.3	343.6	340.3	341.5	344.1	344.8
35°	360.5	355.3	344.8	328.4	318.0	316.6	318.6	320.6	320.6
37.5°	325.8	320.6	313.4	300.2	292.4	293.0	295.7	298.3	300.2
40°	291.8	287.8	282.6	272.1	266.2	268.8	272.1	274.7	277.3
42.5°	261.6	257.6	253.7	245.8	241.9	245.2	249.1	251.7	254.3
45°	234.1	231.5	227.5	220.9	218.3	221.6	226.1	228.9	231.5
47.5°	210.4	209.2	203.9	198.0	196.6	199.9	203.9	207.1	209.2
50°	188.8	186.9	182.3	176.4	175.0	180.3	182.9	184.9	186.9
52.5°	167.9	165.8	160.6	155.3	155.3	159.3	161.3	161.9	163.9
55°	149.4	147.5	142.2	138.4	137.0	140.3	141.6	141.6	142.9
57.5°	132.5	130.4	125.2	120.6	119.9	122.0	122.0	122.0	122.6
60°	116.1	114.0	108.8	104.9	103.6	104.2	103.6	102.9	103.6
62.5°	100.9	99.0	93.8	89.1	87.9	87.9	85.9	85.2	85.9
65°	87.2	83.9	80.0	75.3	72.7	70.8	68.2	68.2	68.2
67.5°	73.4	70.8	66.2	61.7	58.4	55.1	51.1	52.5	53.1
70°	61.0	58.9	53.7	49.2	44.6	40.6	37.3	38.7	39.4
72.5°	49.8	47.2	42.6	37.3	33.5	28.2	26.2	27.5	27.5
75°	38.7	36.1	32.1	26.9	22.3	17.8	17.8	18.3	18.3
77.5°	28.8	26.2	22.3	17.8	13.8	10.5	11.2	11.2	11.2
80°	19.7	17.8	14.5	10.5	7.2	5.9	5.9	5.9	6.6
82.5°	11.2	9.8	7.9	5.2	3.3	3.3	3.3	3.3	3.3
85°	5.2	4.0	3.3	1.9	1.4	1.4	1.4	1.4	1.4
87.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)