

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579809

Luminaire Tested: **HCC4S10D010SL-HM40525935-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579809
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S10D010SL-HM40525935-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 990.8 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579809
CATALOG NUMBER: HCC4S10D010SL-HM40525935-41WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P579809

CATALOG NUMBER: HCC4S10D010SL-HM40525935-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75					75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58					58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51					51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46					46			
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41					41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37					37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34					34			
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63005	63005	63005
5°	66267	62924	60571
10°	68586	62186	57827
15°	70680	61052	55357
20°	70763	58543	52163
25°	68103	54725	48913
30°	63238	50348	45676
35°	56692	45324	42267
40°	49738	40447	39063
45°	43470	35812	36021
50°	38398	31336	32468
55°	33848	27784	29203
60°	30269	24595	25582
65°	26793	21627	21627
70°	23442	18465	18465
75°	20016	15632	17538
80°	15840	13993	15840
85°	10190	12029	14860



TEST NUMBER: P579809
 CATALOG NUMBER: HCC4S10D010SL-HM40525935-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	4.9
10°-20°	136.3	13.8
20°-30°	191.0	19.3
30°-40°	196.7	19.9
40°-50°	167.5	16.9
50°-60°	124.1	12.5
60°-70°	77.9	7.9
70°-80°	38.7	3.9
80°-90°	10.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	375.7	37.9
0°-40°	572.4	57.8
0°-60°	864.1	87.2
0°-90°	990.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	990.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	511	511	511	511	511	
5°	535	526	508	494	489	51
15°	554	529	478	443	434	156
25°	500	466	402	367	359	229
35°	376	348	301	281	281	235
45°	249	232	205	201	206	193
55°	157	145	129	132	136	142
65°	92	83	74	73	74	92
75°	42	37	33	35	37	45
85°	7	7	8	10	10	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579809

CATALOG NUMBER: HCC4S10D010SL-HM40525935-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	522.0	520.1	517.4	512.9	508.2	504.4	500.4	498.4	497.8
5°	535.2	531.2	526.0	517.4	508.2	500.4	493.9	490.6	489.2
7.5°	544.3	540.4	531.9	518.8	505.6	493.9	483.3	478.8	477.5
10°	547.6	543.1	531.2	513.5	496.5	482.1	470.2	464.3	461.7
12.5°	550.2	544.3	529.3	508.2	487.3	469.5	457.1	449.3	447.2
15°	553.5	546.9	528.6	503.0	478.1	457.1	443.4	436.1	433.5
17.5°	550.2	543.1	521.4	492.5	464.3	441.4	426.3	419.7	417.1
20°	539.1	531.2	507.0	476.1	446.0	422.3	407.3	400.7	397.4
22.5°	522.0	513.5	488.5	455.8	424.9	402.1	387.6	381.0	379.1
25°	500.4	491.8	465.7	432.2	402.1	379.8	367.2	361.3	359.4
27.5°	474.8	466.4	440.7	408.0	379.1	358.1	348.2	342.3	341.1
30°	444.0	435.5	410.6	380.4	353.5	333.8	325.9	321.4	320.7
32.5°	409.9	402.7	379.8	352.2	326.6	310.2	304.3	301.0	300.3
35°	376.5	368.6	348.2	323.3	301.0	286.5	281.3	280.7	280.7
37.5°	342.3	334.5	318.1	295.1	276.1	263.0	261.1	261.6	261.6
40°	308.9	301.7	287.2	268.2	251.2	241.4	240.7	242.1	242.6
42.5°	277.4	271.5	258.4	242.1	227.6	219.7	220.3	222.9	225.0
45°	249.2	244.0	232.2	217.7	205.3	199.4	201.3	204.6	206.5
47.5°	223.6	219.1	207.9	194.8	184.2	180.4	183.0	186.9	189.6
50°	200.1	196.1	185.6	171.8	163.3	160.7	164.0	167.9	169.2
52.5°	179.0	175.1	164.0	152.2	145.6	144.3	147.6	150.9	152.8
55°	157.4	154.1	145.0	134.4	129.2	128.6	131.8	134.4	135.8
57.5°	139.7	136.4	127.9	118.7	114.1	113.5	116.8	118.7	119.4
60°	122.7	119.4	111.5	103.0	99.7	99.7	101.6	103.0	103.7
62.5°	106.9	103.7	96.4	89.2	86.6	86.6	86.6	87.2	89.2
65°	91.8	89.2	82.6	76.1	74.1	72.8	72.8	72.8	74.1
67.5°	78.1	75.4	70.2	64.3	62.2	60.3	59.6	61.0	61.0
70°	65.0	62.9	57.7	53.1	51.2	49.2	48.5	51.2	51.2
72.5°	53.1	51.2	47.9	43.2	41.3	40.6	42.0	43.2	43.9
75°	42.0	40.1	37.3	34.7	32.8	33.5	35.4	36.1	36.8
77.5°	31.5	30.8	28.2	26.3	26.3	26.9	28.2	29.5	30.2
80°	22.3	21.6	20.4	19.0	19.7	20.9	21.6	23.0	22.3
82.5°	13.8	13.8	13.1	13.1	13.8	15.1	15.7	16.4	17.1
85°	7.2	7.2	7.2	7.9	8.5	9.2	9.8	10.5	10.5
87.5°	1.9	2.6	2.6	3.3	4.0	4.0	4.6	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)