

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579804

Luminaire Tested: **HCC4W10D010SL-HM40525935-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010SL-HM40525935-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 977.0 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579804
CATALOG NUMBER: HCC4W10D010SL-HM40525935-41WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579804

CATALOG NUMBER: HCC4W10D010SL-HM40525935-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	78115	78115	78115
5°	77918	78005	78005
10°	77015	77090	77015
15°	76095	76095	76095
20°	72968	73139	73218
25°	68253	68334	68525
30°	61158	61343	61343
35°	49645	50052	50142
40°	37468	37678	37791
45°	28712	28590	28590
50°	23641	23526	23526
55°	20322	20171	20171
60°	18107	17934	17934
65°	17045	17045	17045
70°	15832	15832	15832
75°	14392	14678	14392
80°	13496	12999	13496
85°	11180	11180	11180



TEST NUMBER: P579804
 CATALOG NUMBER: HCC4W10D010SL-HM40525935-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.7	6.1
10°-20°	167.0	17.1
20°-30°	229.4	23.5
30°-40°	206.3	21.1
40°-50°	130.3	13.3
50°-60°	85.1	8.7
60°-70°	57.6	5.9
70°-80°	32.4	3.3
80°-90°	9.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.1	46.7
0°-40°	662.4	67.8
0°-60°	877.8	89.8
0°-90°	977.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	977.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	633	633	633	633	633	
5°	629	629	630	630	630	60
15°	596	596	596	596	596	167
25°	502	502	502	504	504	229
35°	330	331	332	334	333	205
45°	165	164	164	164	164	131
55°	94	94	94	94	94	85
65°	58	58	58	58	58	58
75°	30	31	31	31	30	32
85°	8	8	8	8	8	9
90°	0	0	0	0	0	



TEST NUMBER: P579804

CATALOG NUMBER: HCC4W10D010SL-HM40525935-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	633.3	633.3	633.3	633.3	633.3
2.5°	630.0	630.0	630.0	630.0	630.0
5°	629.3	629.3	630.0	630.0	630.0
7.5°	624.8	625.3	625.3	625.3	625.3
10°	614.9	614.9	615.5	615.5	614.9
12.5°	605.8	605.8	605.8	606.3	605.8
15°	595.9	595.9	595.9	595.9	595.9
17.5°	578.8	579.5	579.5	579.5	579.5
20°	555.9	557.2	557.2	557.8	557.8
22.5°	529.6	530.3	531.0	531.7	531.0
25°	501.5	502.1	502.1	503.5	503.5
27.5°	468.7	469.3	470.7	470.7	470.7
30°	429.4	430.1	430.7	430.7	430.7
32.5°	382.8	382.8	384.2	384.8	384.2
35°	329.7	331.0	332.4	333.7	333.0
37.5°	279.3	280.5	281.2	281.2	281.9
40°	232.7	234.0	234.0	235.3	234.7
42.5°	196.0	195.4	195.4	196.6	196.0
45°	164.6	163.9	163.9	163.9	163.9
47.5°	141.6	140.9	140.9	140.9	140.9
50°	123.2	122.6	122.6	122.6	122.6
52.5°	108.1	107.5	107.5	107.5	106.9
55°	94.5	94.5	93.8	94.5	93.8
57.5°	81.9	81.9	81.9	81.9	81.9
60°	73.4	72.7	72.7	72.7	72.7
62.5°	65.5	65.5	65.5	65.5	65.5
65°	58.4	58.4	58.4	58.4	58.4
67.5°	51.1	50.5	51.1	51.1	50.5
70°	43.9	43.2	43.9	43.9	43.9
72.5°	36.8	36.8	36.8	37.3	36.8
75°	30.2	30.8	30.8	30.8	30.2
77.5°	24.2	24.9	24.2	24.2	24.2
80°	19.0	18.3	18.3	18.3	19.0
82.5°	13.1	13.1	13.1	13.1	13.1
85°	7.9	7.9	7.9	7.9	7.9
87.5°	3.3	3.3	3.3	3.3	3.3
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)