

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579845

Luminaire Tested: **HCC4W15D010SL-HM40525827-41WWWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579845  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W15D010SL-HM40525827-41WWWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1343.6 lumens  
Efficiency: N/A  
Efficacy: 96.0 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579845  
CATALOG NUMBER: HCC4W15D010SL-HM40525827-41WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P579845

CATALOG NUMBER: HCC4W15D010SL-HM40525827-41WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46			
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34			
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	85454	85454	85454
5°	89854	85335	82140
10°	93009	84317	78418
15°	95849	82786	75060
20°	95965	79387	70737
25°	92355	74200	66320
30°	85741	68280	61942
35°	76870	61466	57325
40°	67450	54842	52974
45°	58942	48546	48877
50°	52060	42504	44020
55°	45891	37676	39590
60°	41025	33353	34660
65°	36337	29332	29332
70°	31736	25028	25028
75°	27165	21207	23733
80°	21452	18966	21452
85°	13869	16417	20096



TEST NUMBER: P579845  
 CATALOG NUMBER: HCC4W15D010SL-HM40525827-41WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.6	4.9
10°-20°	184.8	13.8
20°-30°	259.0	19.3
30°-40°	266.8	19.9
40°-50°	227.1	16.9
50°-60°	168.3	12.5
60°-70°	105.6	7.9
70°-80°	52.5	3.9
80°-90°	13.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	509.5	37.9
0°-40°	776.3	57.8
0°-60°	1171.7	87.2
0°-90°	1343.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1343.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	693	693	693	693	693	
5°	726	713	689	670	663	70
15°	751	717	648	601	588	211
25°	679	632	545	498	487	310
35°	510	472	408	382	381	318
45°	338	315	278	273	280	262
55°	213	197	175	179	184	193
65°	124	112	100	99	100	124
75°	57	51	44	48	50	61
85°	10	10	12	13	14	13
90°	0	0	0	0	0	



TEST NUMBER: P579845

CATALOG NUMBER: HCC4W15D010SL-HM40525827-41WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	692.8	692.8	692.8	692.8	692.8	692.8	692.8	692.8	692.8
2.5°	707.9	705.3	701.6	695.5	689.2	683.9	678.6	675.9	675.0
5°	725.7	720.4	713.2	701.6	689.2	678.6	669.7	665.3	663.4
7.5°	738.1	732.8	721.3	703.5	685.7	669.7	655.5	649.2	647.4
10°	742.6	736.4	720.4	696.4	673.2	653.7	637.6	629.7	626.1
12.5°	746.2	738.1	717.7	689.2	660.8	636.7	619.9	609.2	606.6
15°	750.6	741.7	716.8	682.1	648.3	619.9	601.2	591.5	587.8
17.5°	746.2	736.4	707.0	667.9	629.7	598.5	578.1	569.2	565.7
20°	731.1	720.4	687.4	645.7	604.8	572.7	552.2	543.4	538.9
22.5°	707.9	696.4	662.5	618.1	576.3	545.2	525.6	516.8	514.0
25°	678.6	667.0	631.5	586.1	545.2	514.9	498.0	490.0	487.3
27.5°	643.9	632.3	597.6	553.2	514.0	485.6	472.2	464.2	462.4
30°	602.0	590.6	556.8	515.9	479.4	452.6	442.0	435.8	434.9
32.5°	555.9	546.1	514.9	477.5	442.9	420.7	412.6	408.2	407.3
35°	510.5	499.8	472.2	438.4	408.2	388.6	381.6	380.7	380.7
37.5°	464.2	453.5	431.4	400.2	374.4	356.7	353.9	354.9	354.9
40°	418.9	409.1	389.5	363.7	340.6	327.2	326.4	328.1	329.0
42.5°	376.2	368.2	350.4	328.1	308.6	297.9	298.8	302.3	305.1
45°	337.9	330.9	314.8	295.3	278.3	270.4	273.0	277.4	280.2
47.5°	303.2	297.1	282.0	264.1	249.9	244.6	248.1	253.4	257.1
50°	271.3	265.9	251.7	233.0	221.5	217.8	222.3	227.6	229.4
52.5°	242.7	237.4	222.3	206.4	197.4	195.7	200.1	204.5	207.3
55°	213.4	209.0	196.6	182.3	175.2	174.3	178.7	182.3	184.1
57.5°	189.4	185.0	173.4	161.0	154.7	153.8	158.3	161.0	161.9
60°	166.3	161.9	151.2	139.6	135.2	135.2	137.8	139.6	140.5
62.5°	145.0	140.5	130.8	121.0	117.3	117.3	117.3	118.2	121.0
65°	124.5	121.0	112.1	103.1	100.5	98.7	98.7	98.7	100.5
67.5°	105.9	102.3	95.2	87.2	84.5	81.9	81.0	82.7	82.7
70°	88.0	85.4	78.2	72.1	69.4	66.7	65.8	69.4	69.4
72.5°	72.1	69.4	64.9	58.7	56.1	55.1	57.0	58.7	59.6
75°	57.0	54.2	50.7	47.2	44.5	45.4	48.0	48.9	49.8
77.5°	42.6	41.8	38.2	35.6	35.6	36.5	38.2	40.0	40.9
80°	30.2	29.3	27.5	25.8	26.7	28.4	29.3	31.2	30.2
82.5°	18.6	18.6	17.7	17.7	18.6	20.5	21.4	22.3	23.1
85°	9.8	9.8	9.8	10.7	11.6	12.5	13.3	14.2	14.2
87.5°	2.6	3.5	3.5	4.4	5.3	5.3	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)