

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579790

Luminaire Tested: **HCC4S10D010BZ-HM40525930-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S10D010BZ-HM40525930-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 945.0 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579790
CATALOG NUMBER: HCC4S10D010BZ-HM40525930-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579790

CATALOG NUMBER: HCC4S10D010BZ-HM40525930-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76				
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66				
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58				
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52				
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47				
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42				42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38				
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35				
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	65275	65275	65275
5°	68136	64979	61970
10°	69864	63626	58078
15°	71306	61920	53901
20°	70921	58910	49354
25°	67940	54480	44898
30°	62768	49750	40706
35°	55021	44240	36846
40°	47918	39079	33185
45°	41708	34102	29637
50°	37150	29398	26155
55°	33203	25849	22644
60°	29652	22572	19513
65°	26326	19788	18533
70°	23117	17058	17275
75°	19587	14535	16013
80°	15059	12360	14633
85°	8916	9624	12454



TEST NUMBER: P579790
 CATALOG NUMBER: HCC4S10D010BZ-HM40525930-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	5.2
10°-20°	136.8	14.5
20°-30°	186.9	19.8
30°-40°	187.7	19.9
40°-50°	155.3	16.4
50°-60°	112.5	11.9
60°-70°	71.3	7.5
70°-80°	36.0	3.8
80°-90°	8.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	373.3	39.5
0°-40°	561.0	59.4
0°-60°	828.8	87.7
0°-90°	945.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	945.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	529	529	529	529	529	
5°	550	542	525	507	500	53
15°	558	537	485	440	422	157
25°	499	466	400	350	330	228
35°	365	344	294	258	245	229
45°	239	225	196	176	170	186
55°	154	141	120	110	105	139
65°	90	80	68	61	64	90
75°	41	36	30	32	34	44
85°	6	6	7	8	9	9
90°	0	0	0	0	0	



TEST NUMBER: P579790

CATALOG NUMBER: HCC4S10D010BZ-HM40525930-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	529.2	529.2	529.2	529.2	529.2	529.2	529.2	529.2	529.2
2.5°	539.1	537.2	534.2	530.4	526.1	521.1	516.7	514.3	513.0
5°	550.3	547.8	542.3	534.2	524.8	515.5	507.3	502.4	500.5
7.5°	557.2	553.4	545.3	532.9	518.6	504.9	493.1	486.2	484.3
10°	557.8	553.4	542.8	526.1	508.0	489.9	475.6	465.7	463.7
12.5°	558.4	552.8	539.8	519.8	497.4	475.0	457.6	445.8	442.6
15°	558.4	552.8	536.7	513.0	484.9	459.4	440.2	426.4	422.1
17.5°	553.4	547.3	527.9	500.5	470.0	441.4	419.0	404.7	400.3
20°	540.3	533.5	511.8	481.8	448.8	419.0	396.6	381.6	376.0
22.5°	521.7	513.6	490.6	458.2	425.2	394.7	372.9	357.3	352.3
25°	499.2	491.2	466.2	434.5	400.3	371.7	349.8	335.6	329.9
27.5°	471.9	463.2	438.9	407.2	375.4	346.7	326.8	313.7	308.2
30°	440.7	431.4	408.4	377.9	349.3	321.8	302.6	292.0	285.8
32.5°	404.7	396.6	376.0	348.6	321.8	295.7	279.5	270.2	265.2
35°	365.4	361.1	343.7	320.0	293.8	272.1	257.8	249.0	244.7
37.5°	330.6	326.3	311.2	291.3	268.3	248.4	236.6	229.1	225.3
40°	297.6	293.8	279.5	262.8	242.7	225.3	215.4	209.8	206.1
42.5°	265.2	263.3	251.5	235.9	218.5	203.6	195.5	191.1	188.0
45°	239.1	236.6	225.3	210.4	195.5	183.0	176.2	173.1	169.9
47.5°	216.0	212.9	201.1	188.0	174.3	163.1	156.9	153.7	152.5
50°	193.6	190.5	179.9	166.8	153.2	145.1	140.1	137.0	136.3
52.5°	173.7	170.6	158.8	146.3	135.8	128.8	124.5	121.4	120.2
55°	154.4	150.7	140.7	128.8	120.2	113.9	109.6	106.4	105.3
57.5°	137.0	133.3	124.5	113.3	105.3	99.6	95.8	92.7	91.5
60°	120.2	117.0	108.9	98.3	91.5	86.5	82.8	80.3	79.1
62.5°	104.6	102.1	94.0	84.7	79.1	74.7	71.6	69.1	70.3
65°	90.2	87.7	80.3	72.3	67.8	63.5	61.0	61.0	63.5
67.5°	76.6	74.1	67.8	61.0	57.2	54.2	52.3	54.2	56.0
70°	64.1	61.7	56.0	50.4	47.3	44.8	44.8	46.7	47.9
72.5°	52.3	49.8	45.4	41.1	38.6	36.8	38.6	39.8	41.1
75°	41.1	39.3	35.5	32.3	30.5	29.9	31.8	33.0	33.6
77.5°	30.5	29.2	26.7	24.2	23.0	23.7	25.5	26.2	26.7
80°	21.2	20.6	18.7	17.4	17.4	18.1	19.3	19.9	20.6
82.5°	13.1	13.1	11.8	11.2	11.8	13.1	13.7	14.3	14.3
85°	6.3	6.8	6.3	6.3	6.8	8.1	8.1	8.8	8.8
87.5°	1.8	1.8	2.5	2.5	3.1	3.1	3.1	3.1	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)