

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579787

Luminaire Tested: **HCC4W10D010MW-HM40525930-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010MW-HM40525930-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 959.9 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579787
CATALOG NUMBER: HCC4W10D010MW-HM40525930-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P579787

CATALOG NUMBER: HCC4W10D010MW-HM40525930-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88				
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76				76				
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				67				
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58				
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52				52				
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46				46				
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41				41				
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37				37				
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34				34				
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31				31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	56825	56825	56825
5°	59123	57352	56733
10°	61046	57852	56600
15°	63197	58025	56608
20°	63413	56626	55878
25°	61162	53785	54221
30°	56928	50106	51516
35°	51272	45836	47522
40°	45197	41703	43587
45°	39527	37574	39423
50°	35001	33811	35596
55°	30795	29848	31053
60°	27481	25483	26248
65°	24166	20722	20372
70°	21097	15255	13921
75°	17538	9198	7435
80°	13283	3552	2202
85°	6085	849	849



TEST NUMBER: P579787
 CATALOG NUMBER: HCC4W10D010MW-HM40525930-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	4.6
10°-20°	129.7	13.5
20°-30°	187.8	19.6
30°-40°	198.1	20.6
40°-50°	171.5	17.9
50°-60°	127.0	13.2
60°-70°	73.2	7.6
70°-80°	25.6	2.7
80°-90°	2.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	361.9	37.7
0°-40°	560.0	58.3
0°-60°	858.4	89.4
0°-90°	959.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	461	461	461	461	461	
5°	478	471	463	459	458	46
15°	495	479	454	444	443	139
25°	449	427	395	393	398	206
35°	340	325	304	311	316	213
45°	227	220	215	224	226	176
55°	143	140	139	144	144	129
65°	83	78	71	67	70	83
75°	37	31	19	16	16	40
85°	4	2	1	1	1	7
90°	0	0	0	0	0	



TEST NUMBER: P579787

CATALOG NUMBER: HCC4W10D010MW-HM40525930-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	460.7	460.7	460.7	460.7	460.7	460.7	460.7	460.7	460.7
2.5°	467.5	466.2	464.4	461.9	459.4	457.5	456.9	456.3	456.3
5°	477.5	475.0	471.2	466.2	463.2	461.2	459.4	458.2	458.2
7.5°	484.3	481.8	476.3	469.3	465.0	461.2	458.7	456.9	456.9
10°	487.4	484.3	477.5	468.7	461.9	456.9	453.2	451.9	451.9
12.5°	491.2	487.4	478.1	466.9	458.2	451.9	448.1	446.9	446.9
15°	494.9	490.5	478.6	465.7	454.4	446.9	443.8	443.3	443.3
17.5°	493.0	487.4	473.7	458.2	445.8	438.2	435.2	435.2	435.7
20°	483.1	477.5	461.9	444.5	431.4	425.7	423.3	424.6	425.7
22.5°	468.1	461.2	444.5	427.7	414.0	409.0	409.0	410.8	412.8
25°	449.4	443.3	427.0	408.3	395.2	391.6	392.8	395.9	398.4
27.5°	428.2	421.4	404.7	387.1	374.1	372.2	375.3	379.8	381.0
30°	399.7	394.1	379.8	362.9	351.8	351.1	355.4	358.6	361.7
32.5°	372.2	366.0	352.3	336.2	328.1	328.7	333.7	337.4	339.2
35°	340.5	334.9	324.9	311.8	304.4	305.7	311.2	315.0	315.6
37.5°	310.7	306.9	296.9	287.0	281.3	283.8	288.8	293.1	293.1
40°	280.7	277.7	270.2	262.1	259.0	262.1	267.1	270.7	270.7
42.5°	252.1	250.2	244.0	238.4	236.6	240.9	245.2	248.4	247.7
45°	226.6	224.8	220.3	216.0	215.4	219.7	223.5	225.3	226.0
47.5°	203.6	202.3	198.6	195.5	195.5	199.8	202.9	204.8	205.4
50°	182.4	181.2	178.0	175.6	176.2	180.5	183.0	184.9	185.5
52.5°	161.3	160.6	158.1	155.0	156.8	160.0	163.1	164.3	165.0
55°	143.2	143.2	140.1	137.6	138.8	141.9	143.8	144.4	144.4
57.5°	127.0	126.3	122.7	120.2	120.7	123.9	125.1	125.7	125.7
60°	111.4	110.8	107.1	103.3	103.3	105.2	105.8	106.4	106.4
62.5°	96.5	95.8	91.5	88.4	87.2	86.5	86.5	87.7	90.2
65°	82.8	82.2	77.8	72.8	71.0	69.1	67.3	68.5	69.8
67.5°	70.3	69.1	64.8	60.4	56.0	52.9	49.8	51.7	54.2
70°	58.5	57.2	52.2	47.3	42.3	37.3	34.8	37.3	38.6
72.5°	47.3	46.1	41.1	36.1	29.9	24.9	24.2	24.9	25.5
75°	36.8	36.1	31.2	25.5	19.3	15.6	15.6	15.6	15.6
77.5°	27.4	26.2	21.2	16.2	11.2	8.8	8.1	8.1	8.1
80°	18.7	17.4	13.1	9.3	5.0	3.8	3.8	3.1	3.1
82.5°	10.6	10.0	6.8	3.8	1.8	1.3	1.3	1.3	1.3
85°	4.3	3.8	2.5	1.3	0.6	0.6	0.6	0.6	0.6
87.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)