

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579837

Luminaire Tested: **HCC4S15D010SL-HM40525827-41MDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579837  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S15D010SL-HM40525827-41MDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1283.9 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579837  
CATALOG NUMBER: HCC4S15D010SL-HM40525827-41MDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579837

CATALOG NUMBER: HCC4S15D010SL-HM40525827-41MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47	47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40	40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	108853
5°	108290
10°	106311
15°	104060
20°	99601
25°	92628
30°	81995
35°	64703
40°	48418
45°	37242
50°	30223
55°	25053
60°	22153
65°	20518
70°	18934
75°	17395
80°	15840
85°	12596



TEST NUMBER: P579837  
 CATALOG NUMBER: HCC4S15D010SL-HM40525827-41MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.7	6.4
10°-20°	228.5	17.8
20°-30°	310.3	24.2
30°-40°	268.8	20.9
40°-50°	168.8	13.1
50°-60°	106.1	8.3
60°-70°	69.7	5.4
70°-80°	38.4	3.0
80°-90°	10.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	621.5	48.4
0°-40°	890.3	69.3
0°-60°	1165.2	90.8
0°-90°	1283.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1283.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	882	
5°	875	83
15°	815	229
25°	681	310
35°	430	269
45°	214	169
55°	116	106
65°	70	70
75°	36	38
85°	9	11
90°	0	



TEST NUMBER: P579837  
CATALOG NUMBER: HCC4S15D010SL-HM40525827-41MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	882.5
2.5°	877.2
5°	874.6
7.5°	865.6
10°	848.8
12.5°	831.8
15°	814.9
17.5°	791.8
20°	758.8
22.5°	721.5
25°	680.6
27.5°	633.4
30°	575.7
32.5°	505.3
35°	429.7
37.5°	360.3
40°	300.7
42.5°	253.6
45°	213.5
47.5°	183.3
50°	157.5
52.5°	135.2
55°	116.5
57.5°	100.5
60°	89.8
62.5°	80.0
65°	70.3
67.5°	60.5
70°	52.5
72.5°	43.5
75°	36.5
77.5°	28.4
80°	22.3
82.5°	15.1
85°	8.9
87.5°	3.5
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)