

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579862

Luminaire Tested: **HCC4W15D010BZ-HM40525830-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010BZ-HM40525830-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1462.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579862
CATALOG NUMBER: HCC4W15D010BZ-HM40525830-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579862

CATALOG NUMBER: HCC4W15D010BZ-HM40525830-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	100971	100971	100971
5°	105418	100527	95884
10°	108089	98433	89878
15°	110317	95811	83386
20°	109735	91161	76355
25°	105135	84285	69477
30°	97121	76953	62967
35°	85121	68452	56993
40°	74132	60494	51332
45°	64524	52750	45877
50°	57472	45478	40470
55°	51375	39977	35010
60°	45860	34931	30170
65°	40744	30616	28661
70°	35811	26399	26723
75°	30310	22494	24782
80°	23227	19108	22588
85°	13728	15001	19106



TEST NUMBER: P579862
 CATALOG NUMBER: HCC4W15D010BZ-HM40525830-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.7	5.2
10°-20°	211.7	14.5
20°-30°	289.2	19.8
30°-40°	290.4	19.9
40°-50°	240.2	16.4
50°-60°	174.1	11.9
60°-70°	110.3	7.5
70°-80°	55.7	3.8
80°-90°	13.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.6	39.5
0°-40°	868.0	59.4
0°-60°	1282.3	87.7
0°-90°	1462.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1462.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	819	819	819	819	819	
5°	851	839	812	785	774	82
15°	864	830	750	681	653	243
25°	772	721	619	541	510	353
35°	565	532	455	399	378	354
45°	370	349	302	272	263	288
55°	239	218	186	170	163	215
65°	140	124	105	94	98	139
75°	64	55	47	49	52	68
85°	10	10	11	12	14	13
90°	0	0	0	0	0	



TEST NUMBER: P579862

CATALOG NUMBER: HCC4W15D010BZ-HM40525830-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	818.6	818.6	818.6	818.6	818.6	818.6	818.6	818.6	818.6
2.5°	834.1	831.1	826.4	820.6	813.9	806.1	799.4	795.6	793.6
5°	851.4	847.5	838.9	826.4	811.9	797.5	785.0	777.3	774.4
7.5°	862.1	856.3	843.8	824.4	802.3	781.1	762.8	752.2	749.3
10°	863.0	856.3	839.9	813.9	785.9	758.0	735.9	720.4	717.6
12.5°	863.9	855.3	835.0	804.2	769.5	734.8	707.9	689.6	684.8
15°	863.9	855.3	830.2	793.6	750.3	710.9	680.9	659.8	653.0
17.5°	856.3	846.6	816.7	774.4	727.2	682.9	648.2	626.0	619.3
20°	836.0	825.5	791.7	745.5	694.5	648.2	613.5	590.4	581.7
22.5°	807.2	794.6	758.9	708.9	657.9	610.7	576.9	552.8	545.2
25°	772.5	760.0	721.4	672.3	619.3	575.0	541.3	519.2	510.5
27.5°	730.1	716.5	679.0	629.9	580.8	536.4	505.6	485.4	476.7
30°	681.9	667.4	631.8	584.6	540.3	498.0	468.1	451.7	442.1
32.5°	626.0	613.5	581.7	539.4	498.0	457.5	432.4	418.0	410.3
35°	565.3	558.6	531.7	495.0	454.6	420.9	398.7	385.2	378.5
37.5°	511.4	504.7	481.5	450.7	415.1	384.3	366.0	354.4	348.6
40°	460.4	454.6	432.4	406.5	375.7	348.6	333.3	324.6	318.8
42.5°	410.3	407.4	389.1	365.1	338.0	314.9	302.4	295.7	290.8
45°	369.9	366.0	348.6	325.5	302.4	283.1	272.5	267.8	263.0
47.5°	334.2	329.4	311.1	290.8	269.7	252.3	242.7	237.9	235.9
50°	299.5	294.7	278.3	258.1	237.0	224.4	216.7	211.9	210.9
52.5°	268.7	263.9	245.6	226.4	210.0	199.3	192.6	187.8	185.9
55°	238.9	233.1	217.6	199.3	185.9	176.2	169.5	164.8	162.8
57.5°	211.9	206.1	192.6	175.3	162.8	154.1	148.4	143.5	141.6
60°	185.9	181.1	168.5	152.1	141.6	133.8	128.1	124.3	122.3
62.5°	161.8	157.9	145.4	131.0	122.3	115.6	110.7	106.9	108.8
65°	139.6	135.8	124.3	111.8	104.9	98.2	94.4	94.4	98.2
67.5°	118.5	114.6	104.9	94.4	88.6	83.8	81.0	83.8	86.6
70°	99.3	95.4	86.6	78.0	73.2	69.4	69.4	72.2	74.1
72.5°	81.0	77.1	70.3	63.6	59.7	56.8	59.7	61.6	63.6
75°	63.6	60.7	54.9	50.0	47.2	46.3	49.1	51.1	52.0
77.5°	47.2	45.3	41.4	37.5	35.6	36.6	39.5	40.5	41.4
80°	32.7	31.8	28.9	26.9	26.9	28.0	29.9	30.8	31.8
82.5°	20.2	20.2	18.3	17.3	18.3	20.2	21.1	22.2	22.2
85°	9.7	10.6	9.7	9.7	10.6	12.5	12.5	13.5	13.5
87.5°	2.8	2.8	3.9	3.9	4.8	4.8	4.8	4.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)