

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579900

Luminaire Tested: **HCC4W15D010SL-HM40525927-41WDBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579900  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W15D010SL-HM40525927-41WDBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 986.7 lumens  
Efficiency: N/A  
Efficacy: 70.5 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579900  
CATALOG NUMBER: HCC4W15D010SL-HM40525927-41WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P579900  
 CATALOG NUMBER: HCC4W15D010SL-HM40525927-41WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93																																				
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																																				
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78																																				
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72																																				
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																																				
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																																				
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																																				
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52																																				
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49																																				
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	98393
5°	98484
10°	98671
15°	100127
20°	97632
25°	91593
30°	81013
35°	61616
40°	38805
45°	22293
50°	11821
55°	4925
60°	1307
65°	1109
70°	829
75°	715
80°	568
85°	1132



TEST NUMBER: P579900  
 CATALOG NUMBER: HCC4W15D010SL-HM40525927-41WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.7	7.7
10°-20°	219.5	22.3
20°-30°	306.4	31.1
30°-40°	252.1	25.6
40°-50°	103.9	10.5
50°-60°	23.4	2.4
60°-70°	3.8	0.4
70°-80°	1.4	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.6	61.0
0°-40°	853.7	86.5
0°-60°	981.0	99.4
0°-90°	986.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	986.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	798	
5°	795	76
15°	784	220
25°	673	306
35°	409	252
45°	128	104
55°	23	23
65°	4	4
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P579900  
CATALOG NUMBER: HCC4W15D010SL-HM40525927-41WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	797.7
2.5°	794.0
5°	795.4
7.5°	792.5
10°	787.8
12.5°	785.6
15°	784.1
17.5°	770.4
20°	743.8
22.5°	710.3
25°	673.0
27.5°	628.2
30°	568.8
32.5°	495.8
35°	409.2
37.5°	321.7
40°	241.0
42.5°	175.7
45°	127.8
47.5°	91.3
50°	61.6
52.5°	38.8
55°	22.9
57.5°	11.4
60°	5.3
62.5°	4.5
65°	3.8
67.5°	3.1
70°	2.3
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)