

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579858

Luminaire Tested: **HCC4W15D010MW-HM40525830-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010MW-HM40525830-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1435.1 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579858
CATALOG NUMBER: HCC4W15D010MW-HM40525830-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P579858

CATALOG NUMBER: HCC4W15D010MW-HM40525830-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89					89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78					78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69					69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62					62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56					56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51					51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46					46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42					42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39					39			
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36					36			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	114724	114724	114724
5°	114444	114568	114568
10°	113112	113237	113112
15°	111773	111773	111773
20°	107175	107425	107543
25°	100235	100385	100644
30°	89829	90099	90099
35°	72909	73497	73647
40°	55035	55341	55502
45°	42161	41987	41987
50°	34732	34560	34560
55°	29805	29612	29612
60°	26593	26371	26371
65°	25012	25012	25012
70°	23261	23261	23261
75°	21112	21589	21112
80°	19889	19108	19889
85°	16417	16417	16417



TEST NUMBER: P579858
 CATALOG NUMBER: HCC4W15D010MW-HM40525830-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.6	6.1
10°-20°	245.2	17.1
20°-30°	337.0	23.5
30°-40°	303.0	21.1
40°-50°	191.5	13.3
50°-60°	125.0	8.7
60°-70°	84.7	5.9
70°-80°	47.7	3.3
80°-90°	13.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.9	46.7
0°-40°	972.8	67.8
0°-60°	1289.3	89.8
0°-90°	1435.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1435.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	930	930	930	930	930	
5°	924	924	925	925	925	88
15°	875	875	875	875	875	245
25°	736	738	738	740	740	336
35°	484	486	488	490	489	301
45°	242	241	241	241	241	192
55°	139	139	138	139	138	125
65°	86	86	86	86	86	85
75°	44	45	45	45	44	47
85°	12	12	12	12	12	13
90°	0	0	0	0	0	



TEST NUMBER: P579858

CATALOG NUMBER: HCC4W15D010MW-HM40525830-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	930.1	930.1	930.1	930.1	930.1
2.5°	925.3	925.3	925.3	925.3	925.3
5°	924.3	924.3	925.3	925.3	925.3
7.5°	917.6	918.6	918.6	918.6	918.6
10°	903.1	903.1	904.1	904.1	903.1
12.5°	889.7	889.7	889.7	890.6	889.7
15°	875.3	875.3	875.3	875.3	875.3
17.5°	850.1	851.2	851.2	851.2	851.2
20°	816.5	818.4	818.4	819.3	819.3
22.5°	777.9	779.0	779.9	780.9	779.9
25°	736.5	737.6	737.6	739.5	739.5
27.5°	688.5	689.4	691.3	691.3	691.3
30°	630.7	631.6	632.6	632.6	632.6
32.5°	562.2	562.2	564.2	565.2	564.2
35°	484.2	486.2	488.1	490.0	489.1
37.5°	410.1	412.0	413.1	413.1	414.0
40°	341.8	343.7	343.7	345.6	344.7
42.5°	287.9	287.0	287.0	288.8	287.9
45°	241.7	240.7	240.7	240.7	240.7
47.5°	208.0	207.0	207.0	207.0	207.0
50°	181.0	180.1	180.1	180.1	180.1
52.5°	158.8	157.9	157.9	157.9	156.9
55°	138.6	138.6	137.7	138.6	137.7
57.5°	120.4	120.4	120.4	120.4	120.4
60°	107.8	106.9	106.9	106.9	106.9
62.5°	96.3	96.3	96.3	96.3	96.3
65°	85.7	85.7	85.7	85.7	85.7
67.5°	75.2	74.1	75.2	75.2	74.1
70°	64.5	63.6	64.5	64.5	64.5
72.5°	53.9	53.9	53.9	54.9	53.9
75°	44.3	45.3	45.3	45.3	44.3
77.5°	35.6	36.6	35.6	35.6	35.6
80°	28.0	26.9	26.9	26.9	28.0
82.5°	19.2	19.2	19.2	19.2	19.2
85°	11.6	11.6	11.6	11.6	11.6
87.5°	4.8	4.8	4.8	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)