

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579915

Luminaire Tested: **HCC4W15D010MB-HM40525927-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010MB-HM40525927-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 923.6 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579915
CATALOG NUMBER: HCC4W15D010MB-HM40525927-41WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P579915

CATALOG NUMBER: HCC4W15D010MB-HM40525927-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	65941	65941	65941
5°	69870	65734	62441
10°	72782	64678	58767
15°	75558	63133	55254
20°	76276	60105	51113
25°	73792	55582	46790
30°	69006	50362	42572
35°	61496	44767	38247
40°	53763	38934	34055
45°	46819	33038	29445
50°	40873	28016	25253
55°	35827	23225	20451
60°	31330	18773	14999
65°	27318	13980	8435
70°	23874	9052	2741
75°	19539	4718	715
80°	14633	2202	568
85°	8633	1132	1132



TEST NUMBER: P579915
 CATALOG NUMBER: HCC4W15D010MB-HM40525927-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.5	5.5
10°-20°	141.2	15.3
20°-30°	195.3	21.1
30°-40°	196.3	21.3
40°-50°	158.4	17.2
50°-60°	107.1	11.6
60°-70°	54.5	5.9
70°-80°	17.5	1.9
80°-90°	2.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.0	41.9
0°-40°	583.3	63.2
0°-60°	848.9	91.9
0°-90°	923.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	923.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	535	535	535	535	535	
5°	564	554	531	512	504	54
15°	592	560	494	447	433	167
25°	542	495	408	358	344	248
35°	408	369	297	260	254	255
45°	268	240	189	169	169	208
55°	167	144	108	94	95	150
65°	94	76	48	31	29	94
75°	41	29	10	2	2	44
85°	6	3	1	1	1	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579915

CATALOG NUMBER: HCC4W15D010MB-HM40525927-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	534.6	534.6	534.6	534.6	534.6	534.6	534.6	534.6	534.6
2.5°	549.2	546.1	543.0	537.7	531.7	525.5	521.8	518.7	517.2
5°	564.3	560.5	553.7	542.2	530.9	520.2	511.9	506.5	504.3
7.5°	576.5	571.2	559.7	543.8	526.3	509.6	498.9	491.3	488.2
10°	581.1	575.0	559.7	538.5	516.4	495.8	480.7	473.1	469.2
12.5°	586.4	579.5	560.5	533.9	506.5	482.2	464.7	454.8	451.0
15°	591.7	582.6	559.7	527.1	494.4	466.2	447.2	437.3	432.7
17.5°	591.7	581.1	553.7	515.6	478.3	448.8	427.4	416.0	412.3
20°	581.1	569.0	539.3	497.4	457.9	425.9	405.3	394.0	389.4
22.5°	564.3	550.6	518.7	475.4	433.5	402.4	381.8	371.1	366.6
25°	542.2	528.6	495.2	450.3	408.4	377.3	358.3	348.4	343.8
27.5°	516.4	501.2	467.8	422.9	381.8	352.1	334.6	325.5	321.8
30°	484.5	470.0	437.3	393.2	353.6	326.3	310.3	302.0	298.9
32.5°	447.2	435.0	403.1	362.0	324.7	299.7	285.2	278.3	275.3
35°	408.4	397.0	368.8	330.9	297.3	273.8	260.1	255.6	254.0
37.5°	371.9	362.0	334.6	299.7	269.2	248.7	236.5	233.5	231.9
40°	333.9	327.0	302.0	270.0	241.8	223.6	213.8	211.5	211.5
42.5°	299.7	292.1	270.0	241.0	216.0	197.7	190.9	188.6	189.4
45°	268.4	260.8	240.4	213.8	189.4	174.2	168.8	168.8	168.8
47.5°	239.6	232.7	213.8	186.4	166.6	154.4	149.1	149.1	149.9
50°	213.0	208.4	187.2	163.5	146.0	134.6	130.9	130.1	131.6
52.5°	187.8	182.5	163.5	142.2	125.5	116.3	112.6	111.8	112.6
55°	166.6	160.4	143.7	123.3	108.0	98.9	94.3	93.6	95.1
57.5°	146.0	141.4	123.9	105.7	91.3	82.1	78.3	76.9	77.5
60°	127.0	122.5	106.4	89.0	76.1	67.0	61.6	60.0	60.8
62.5°	109.5	105.7	90.5	73.8	60.8	52.5	47.2	43.3	44.9
65°	93.6	89.7	76.1	59.4	47.9	38.8	31.2	28.1	28.9
67.5°	79.8	75.3	62.4	47.2	35.7	25.8	17.5	15.9	15.9
70°	66.2	61.6	50.1	36.5	25.1	13.6	7.6	7.6	7.6
72.5°	53.2	49.5	38.8	27.4	15.9	6.1	3.1	3.1	3.1
75°	41.0	38.0	28.9	19.0	9.9	3.1	2.3	1.5	1.5
77.5°	30.5	27.4	20.6	13.0	6.1	1.5	1.5	1.5	1.5
80°	20.6	18.3	13.6	7.6	3.1	0.8	0.8	0.8	0.8
82.5°	12.2	10.7	7.6	3.8	1.5	0.8	0.8	0.8	0.8
85°	6.1	4.5	3.1	1.5	0.8	0.8	0.8	0.8	0.8
87.5°	1.5	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)