

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579912

Luminaire Tested: **HCC4S15D010MW-HM40525927-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579912
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S15D010MW-HM40525927-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1133.5 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579912
CATALOG NUMBER: HCC4S15D010MW-HM40525927-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P579912

CATALOG NUMBER: HCC4S15D010MW-HM40525927-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	90610	90610	90610
5°	90399	90498	90498
10°	89352	89440	89352
15°	88277	88277	88277
20°	84651	84861	84953
25°	79181	79290	79494
30°	70943	71171	71171
35°	57611	58063	58183
40°	43474	43716	43845
45°	33300	33160	33160
50°	27441	27287	27287
55°	23548	23397	23397
60°	21018	20821	20821
65°	19759	19759	19759
70°	18356	18356	18356
75°	16680	17014	16680
80°	15698	15130	15698
85°	12879	12879	12879



TEST NUMBER: P579912
 CATALOG NUMBER: HCC4S15D010MW-HM40525927-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	6.1
10°-20°	193.7	17.1
20°-30°	266.2	23.5
30°-40°	239.3	21.1
40°-50°	151.2	13.3
50°-60°	98.7	8.7
60°-70°	66.9	5.9
70°-80°	37.6	3.3
80°-90°	10.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.1	46.7
0°-40°	768.4	67.8
0°-60°	1018.4	89.8
0°-90°	1133.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1133.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	735	735	735	735	735	
5°	730	730	731	731	731	69
15°	691	691	691	691	691	194
25°	582	583	583	584	584	266
35°	383	384	386	387	386	238
45°	191	190	190	190	190	151
55°	110	110	109	110	109	99
65°	68	68	68	68	68	67
75°	35	36	36	36	35	37
85°	9	9	9	9	9	11
90°	0	0	0	0	0	



TEST NUMBER: P579912

CATALOG NUMBER: HCC4S15D010MW-HM40525927-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	734.6	734.6	734.6	734.6	734.6
2.5°	730.9	730.9	730.9	730.9	730.9
5°	730.1	730.1	730.9	730.9	730.9
7.5°	724.8	725.5	725.5	725.5	725.5
10°	713.4	713.4	714.1	714.1	713.4
12.5°	702.8	702.8	702.8	703.5	702.8
15°	691.3	691.3	691.3	691.3	691.3
17.5°	671.5	672.3	672.3	672.3	672.3
20°	644.9	646.5	646.5	647.2	647.2
22.5°	614.5	615.2	616.0	616.8	616.0
25°	581.8	582.6	582.6	584.1	584.1
27.5°	543.8	544.5	546.1	546.1	546.1
30°	498.1	498.9	499.7	499.7	499.7
32.5°	444.1	444.1	445.7	446.4	445.7
35°	382.6	384.1	385.6	387.1	386.4
37.5°	323.9	325.5	326.3	326.3	327.0
40°	270.0	271.5	271.5	273.0	272.3
42.5°	227.4	226.6	226.6	228.2	227.4
45°	190.9	190.1	190.1	190.1	190.1
47.5°	164.3	163.5	163.5	163.5	163.5
50°	143.0	142.2	142.2	142.2	142.2
52.5°	125.5	124.7	124.7	124.7	123.9
55°	109.5	109.5	108.8	109.5	108.8
57.5°	95.1	95.1	95.1	95.1	95.1
60°	85.2	84.4	84.4	84.4	84.4
62.5°	76.1	76.1	76.1	76.1	76.1
65°	67.7	67.7	67.7	67.7	67.7
67.5°	59.4	58.6	59.4	59.4	58.6
70°	50.9	50.1	50.9	50.9	50.9
72.5°	42.6	42.6	42.6	43.3	42.6
75°	35.0	35.7	35.7	35.7	35.0
77.5°	28.1	28.9	28.1	28.1	28.1
80°	22.1	21.3	21.3	21.3	22.1
82.5°	15.2	15.2	15.2	15.2	15.2
85°	9.1	9.1	9.1	9.1	9.1
87.5°	3.8	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)