

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579930

Luminaire Tested: **HCC4S15D010MW-HM40525930-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S15D010MW-HM40525930-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1261.0 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579930
CATALOG NUMBER: HCC4S15D010MW-HM40525930-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P579930

CATALOG NUMBER: HCC4S15D010MW-HM40525930-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89					89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78					78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69					69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62					62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56					56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51					51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46					46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42					42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39					39			
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36					36			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	100823	100823	100823
5°	100576	100688	100688
10°	99397	99510	99397
15°	98224	98224	98224
20°	94193	94417	94522
25°	88095	88204	88436
30°	78933	79175	79175
35°	64086	64598	64718
40°	48369	48643	48772
45°	37050	36893	36893
50°	30530	30376	30376
55°	26214	26021	26021
60°	23362	23164	23164
65°	21977	21977	21977
70°	20448	20448	20448
75°	18539	18968	18539
80°	17474	16764	17474
85°	14294	14294	14294



TEST NUMBER: P579930
 CATALOG NUMBER: HCC4S15D010MW-HM40525930-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	6.1
10°-20°	215.5	17.1
20°-30°	296.1	23.5
30°-40°	266.3	21.1
40°-50°	168.3	13.3
50°-60°	109.8	8.7
60°-70°	74.4	5.9
70°-80°	41.9	3.3
80°-90°	11.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	588.7	46.7
0°-40°	854.9	67.8
0°-60°	1133.0	89.8
0°-90°	1261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1261.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	817	817	817	817	817	
5°	812	812	813	813	813	77
15°	769	769	769	769	769	215
25°	647	648	648	650	650	295
35°	426	427	429	431	430	265
45°	212	212	212	212	212	168
55°	122	122	121	122	121	110
65°	75	75	75	75	75	75
75°	39	40	40	40	39	42
85°	10	10	10	10	10	12
90°	0	0	0	0	0	



TEST NUMBER: P579930

CATALOG NUMBER: HCC4S15D010MW-HM40525930-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	817.4	817.4	817.4	817.4	817.4
2.5°	813.2	813.2	813.2	813.2	813.2
5°	812.3	812.3	813.2	813.2	813.2
7.5°	806.4	807.3	807.3	807.3	807.3
10°	793.6	793.6	794.5	794.5	793.6
12.5°	781.8	781.8	781.8	782.7	781.8
15°	769.2	769.2	769.2	769.2	769.2
17.5°	747.1	748.0	748.0	748.0	748.0
20°	717.6	719.3	719.3	720.1	720.1
22.5°	683.7	684.5	685.4	686.2	685.4
25°	647.3	648.1	648.1	649.8	649.8
27.5°	605.0	605.8	607.5	607.5	607.5
30°	554.2	555.1	555.9	555.9	555.9
32.5°	494.1	494.1	495.8	496.6	495.8
35°	425.6	427.3	429.0	430.7	429.8
37.5°	360.4	362.1	363.0	363.0	363.8
40°	300.4	302.1	302.1	303.8	302.9
42.5°	253.0	252.2	252.2	253.9	253.0
45°	212.4	211.5	211.5	211.5	211.5
47.5°	182.7	181.9	181.9	181.9	181.9
50°	159.1	158.3	158.3	158.3	158.3
52.5°	139.6	138.7	138.7	138.7	137.9
55°	121.9	121.9	121.0	121.9	121.0
57.5°	105.7	105.7	105.7	105.7	105.7
60°	94.7	93.9	93.9	93.9	93.9
62.5°	84.6	84.6	84.6	84.6	84.6
65°	75.3	75.3	75.3	75.3	75.3
67.5°	65.9	65.2	65.9	65.9	65.2
70°	56.7	55.8	56.7	56.7	56.7
72.5°	47.4	47.4	47.4	48.2	47.4
75°	38.9	39.8	39.8	39.8	38.9
77.5°	31.3	32.2	31.3	31.3	31.3
80°	24.6	23.6	23.6	23.6	24.6
82.5°	16.9	16.9	16.9	16.9	16.9
85°	10.1	10.1	10.1	10.1	10.1
87.5°	4.2	4.2	4.2	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)