

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579922

Luminaire Tested: **HCC4W15D010MW-HM40525930-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010MW-HM40525930-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1351.6 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579922
CATALOG NUMBER: HCC4W15D010MW-HM40525930-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P579922

CATALOG NUMBER: HCC4W15D010MW-HM40525930-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20								
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92																																				
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84																																				
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76																																				
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69																																				
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63																																				
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58																																				
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53																																				
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49																																				
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45																																				
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113638
5°	114493
10°	115930
15°	118835
20°	119711
25°	116295
30°	106621
35°	87726
40°	63956
45°	41516
50°	23411
55°	11096
60°	4366
65°	2714
70°	1839
75°	1191
80°	568
85°	1132



TEST NUMBER: P579922
 CATALOG NUMBER: HCC4W15D010MW-HM40525930-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.3	6.5
10°-20°	262.4	19.4
20°-30°	389.1	28.8
30°-40°	359.4	26.6
40°-50°	187.7	13.9
50°-60°	51.4	3.8
60°-70°	9.9	0.7
70°-80°	2.8	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	739.8	54.7
0°-40°	1099.3	81.3
0°-60°	1338.4	99.0
0°-90°	1351.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1351.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	921	
5°	925	88
15°	931	262
25°	854	389
35°	583	359
45°	238	188
55°	52	51
65°	9	10
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P579922
CATALOG NUMBER: HCC4W15D010MW-HM40525930-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	921.3
2.5°	918.8
5°	924.7
7.5°	927.3
10°	925.6
12.5°	927.3
15°	930.6
17.5°	927.3
20°	912.0
22.5°	887.4
25°	854.5
27.5°	809.5
30°	748.6
32.5°	671.5
35°	582.6
37.5°	489.5
40°	397.2
42.5°	312.4
45°	238.0
47.5°	174.4
50°	122.0
52.5°	81.3
55°	51.6
57.5°	30.5
60°	17.7
62.5°	12.7
65°	9.3
67.5°	6.8
70°	5.1
72.5°	3.4
75°	2.5
77.5°	1.7
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)