

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579937

Luminaire Tested: **HCC4S15D010MW-HM40525935-41WDWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579937  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S15D010MW-HM40525935-41WDWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1439.0 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579937  
CATALOG NUMBER: HCC4S15D010MW-HM40525935-41WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P579937

CATALOG NUMBER: HCC4S15D010MW-HM40525935-41WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80																			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72																			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65																			
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59																			
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54																			
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49																			
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46																			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42																			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	118128
5°	118691
10°	119512
15°	120712
20°	118700
25°	113219
30°	102875
35°	82983
40°	57579
45°	37801
50°	25330
55°	18021
60°	15394
65°	17687
70°	18970
75°	18253
80°	16479
85°	15143



TEST NUMBER: P579937  
 CATALOG NUMBER: HCC4S15D010MW-HM40525935-41WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.4	6.3
10°-20°	265.5	18.5
20°-30°	379.4	26.4
30°-40°	338.9	23.6
40°-50°	173.8	12.1
50°-60°	79.0	5.5
60°-70°	58.9	4.1
70°-80°	40.1	2.8
80°-90°	11.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	736.3	51.2
0°-40°	1075.2	74.7
0°-60°	1328.1	92.3
0°-90°	1439.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1439.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	958	
5°	959	91
15°	945	266
25°	832	379
35°	551	339
45°	217	174
55°	84	79
65°	61	59
75°	38	40
85°	11	12
90°	0	



TEST NUMBER: P579937  
CATALOG NUMBER: HCC4S15D010MW-HM40525935-41WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	957.7
2.5°	954.2
5°	958.6
7.5°	958.6
10°	954.2
12.5°	949.7
15°	945.3
17.5°	931.9
20°	904.3
22.5°	870.4
25°	831.9
27.5°	783.8
30°	722.3
32.5°	643.9
35°	551.1
37.5°	452.1
40°	357.6
42.5°	279.1
45°	216.7
47.5°	169.4
50°	132.0
52.5°	103.5
55°	83.8
57.5°	70.5
60°	62.4
62.5°	60.6
65°	60.6
67.5°	58.9
70°	52.6
72.5°	45.5
75°	38.3
77.5°	30.4
80°	23.2
82.5°	16.9
85°	10.7
87.5°	4.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)