

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579962

Luminaire Tested: **HCC4S15D010BZ-HM40525940-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S15D010BZ-HM40525940-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1567.7 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579962
CATALOG NUMBER: HCC4S15D010BZ-HM40525940-41WDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579962

CATALOG NUMBER: HCC4S15D010BZ-HM40525940-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																											
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85																											
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77																											
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71																											
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65																											
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60																											
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55																											
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51																											
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47																											
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126639
5°	128509
10°	132538
15°	141616
20°	150045
25°	148414
30°	133212
35°	103672
40°	70235
45°	43853
50°	18978
55°	6365
60°	1603
65°	1109
70°	649
75°	429
80°	639
85°	0



TEST NUMBER: P579962
 CATALOG NUMBER: HCC4S15D010BZ-HM40525940-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.7	6.4
10°-20°	314.8	20.1
20°-30°	493.3	31.5
30°-40°	425.7	27.2
40°-50°	195.8	12.5
50°-60°	33.3	2.1
60°-70°	3.8	0.2
70°-80°	1.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	907.8	57.9
0°-40°	1333.5	85.1
0°-60°	1562.5	99.7
0°-90°	1567.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1567.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1027	
5°	1038	100
15°	1109	315
25°	1090	493
35°	688	426
45°	251	196
55°	30	33
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P579962
CATALOG NUMBER: HCC4S15D010BZ-HM40525940-41WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	1026.7
2.5°	1026.7
5°	1037.9
7.5°	1048.0
10°	1058.2
12.5°	1079.5
15°	1109.0
17.5°	1133.9
20°	1143.1
22.5°	1129.4
25°	1090.5
27.5°	1027.6
30°	935.3
32.5°	818.8
35°	688.5
37.5°	557.2
40°	436.2
42.5°	333.6
45°	251.4
47.5°	176.5
50°	98.9
52.5°	54.6
55°	29.6
57.5°	14.8
60°	6.5
62.5°	4.7
65°	3.8
67.5°	2.7
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)