

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579974

Luminaire Tested: **HCC4W20D010SL-HM40525827-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010SL-HM40525827-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1777.9 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579974
CATALOG NUMBER: HCC4W20D010SL-HM40525827-41MDH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579974

CATALOG NUMBER: HCC4W20D010SL-HM40525827-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																																				
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86																																				
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79																																				
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73																																				
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67																																				
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62																																				
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58																																				
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54																																				
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51																																				
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230151
5°	225334
10°	212947
15°	198888
20°	181902
25°	162445
30°	136403
35°	95963
40°	59190
45°	35428
50°	20897
55°	10408
60°	5378
65°	3502
70°	2200
75°	1763
80°	923
85°	1840



TEST NUMBER: P579974
 CATALOG NUMBER: HCC4W20D010SL-HM40525827-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.0	9.6
10°-20°	435.4	24.5
20°-30°	543.0	30.5
30°-40°	400.0	22.5
40°-50°	164.5	9.3
50°-60°	48.1	2.7
60°-70°	12.3	0.7
70°-80°	3.8	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1148.3	64.6
0°-40°	1548.3	87.1
0°-60°	1760.8	99.0
0°-90°	1777.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1777.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1866	
5°	1820	170
15°	1558	435
25°	1194	543
35°	637	400
45°	203	164
55°	48	48
65°	12	12
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P579974
CATALOG NUMBER: HCC4W20D010SL-HM40525827-41MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1865.9
2.5°	1846.6
5°	1819.9
7.5°	1771.7
10°	1700.2
12.5°	1630.1
15°	1557.5
17.5°	1476.5
20°	1385.8
22.5°	1291.5
25°	1193.6
27.5°	1084.7
30°	957.7
32.5°	804.2
35°	637.3
37.5°	489.8
40°	367.6
42.5°	272.1
45°	203.1
47.5°	149.9
50°	108.9
52.5°	75.0
55°	48.4
57.5°	29.0
60°	21.8
62.5°	15.7
65°	12.0
67.5°	8.5
70°	6.1
72.5°	4.8
75°	3.7
77.5°	2.4
80°	1.3
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)