

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579985

Luminaire Tested: **HCC4W20D010MW-HM40525827-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010MW-HM40525827-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1864.9 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579985
CATALOG NUMBER: HCC4W20D010MW-HM40525827-41RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579985

CATALOG NUMBER: HCC4W20D010MW-HM40525827-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	110382	110382	110382
5°	114852	111398	110209
10°	118610	112385	109968
15°	122768	112731	109960
20°	123189	110010	108580
25°	118840	104509	105339
30°	110581	97321	100084
35°	99607	89051	92334
40°	87818	81007	84695
45°	76787	72984	76578
50°	67987	65685	69158
55°	59804	57998	60342
60°	53384	49511	51016
65°	46931	40248	39547
70°	41005	29644	27048
75°	33980	17871	14440
80°	25714	6819	4333
85°	12029	1840	1840



TEST NUMBER: P579985
 CATALOG NUMBER: HCC4W20D010MW-HM40525827-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.3	4.6
10°-20°	251.9	13.5
20°-30°	364.8	19.6
30°-40°	384.9	20.6
40°-50°	333.1	17.9
50°-60°	246.7	13.2
60°-70°	142.3	7.6
70°-80°	49.7	2.7
80°-90°	5.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	703.0	37.7
0°-40°	1087.9	58.3
0°-60°	1667.8	89.4
0°-90°	1864.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1864.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	895	895	895	895	895	
5°	928	916	900	892	890	89
15°	961	930	883	862	861	270
25°	873	830	768	763	774	400
35°	662	631	591	605	613	413
45°	440	428	418	434	439	342
55°	278	272	270	279	281	251
65°	161	151	138	131	136	161
75°	71	60	38	30	30	77
85°	8	5	1	1	1	13
90°	0	0	0	0	0	



TEST NUMBER: P579985

CATALOG NUMBER: HCC4W20D010MW-HM40525827-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	894.9	894.9	894.9	894.9	894.9	894.9	894.9	894.9	894.9
2.5°	908.2	905.8	902.2	897.3	892.5	888.9	887.7	886.4	886.4
5°	927.6	922.8	915.5	905.8	899.7	896.2	892.5	890.1	890.1
7.5°	940.9	936.1	925.2	911.9	903.4	896.2	891.3	887.7	887.7
10°	947.0	940.9	927.6	910.6	897.3	887.7	880.4	878.0	878.0
12.5°	954.2	947.0	928.8	907.0	890.1	878.0	870.7	868.3	868.3
15°	961.4	952.9	930.0	904.6	882.8	868.3	862.3	861.1	861.1
17.5°	957.9	947.0	920.4	890.1	865.9	851.4	845.3	845.3	846.6
20°	938.5	927.6	897.3	863.5	838.1	827.2	822.4	824.8	827.2
22.5°	909.5	896.2	863.5	830.8	804.3	794.5	794.5	798.2	801.8
25°	873.2	861.1	829.6	793.4	767.9	760.7	763.1	769.2	774.0
27.5°	832.0	818.7	786.0	752.2	726.9	723.2	729.3	737.8	740.2
30°	776.4	765.5	737.8	705.1	683.3	682.1	690.5	696.6	702.7
32.5°	723.2	711.1	684.5	653.1	637.4	638.5	648.2	655.5	659.1
35°	661.5	650.6	631.3	605.8	591.4	593.8	604.7	611.9	613.2
37.5°	603.4	596.2	576.8	557.6	546.7	551.5	561.1	569.6	569.6
40°	545.4	539.3	524.9	509.2	503.1	509.2	518.8	526.0	526.0
42.5°	489.8	486.2	474.1	463.2	459.6	468.0	476.5	482.5	481.3
45°	440.2	436.5	428.1	419.7	418.4	426.9	434.1	437.8	439.0
47.5°	395.5	393.1	385.7	379.8	379.8	388.3	394.2	397.9	399.0
50°	354.3	351.9	345.8	341.0	342.3	350.8	355.6	359.1	360.4
52.5°	313.2	312.0	307.2	301.1	304.8	310.8	316.8	319.3	320.5
55°	278.1	278.1	272.1	267.3	269.7	275.7	279.4	280.6	280.6
57.5°	246.7	245.5	238.2	233.4	234.6	240.6	243.0	244.3	244.3
60°	216.4	215.3	208.1	200.7	200.7	204.4	205.5	206.8	206.8
62.5°	187.4	186.3	177.8	171.7	169.3	168.2	168.2	170.6	175.4
65°	160.8	159.7	151.2	141.5	137.9	134.2	130.6	133.1	135.5
67.5°	136.6	134.2	125.8	117.3	108.9	102.8	96.7	100.4	105.2
70°	113.7	111.3	101.6	91.9	82.2	72.6	67.7	72.6	75.0
72.5°	91.9	89.5	79.8	70.2	58.0	48.4	47.1	48.4	49.6
75°	71.3	70.2	60.4	49.6	37.5	30.3	30.3	30.3	30.3
77.5°	53.2	50.8	41.1	31.4	21.8	17.0	15.7	15.7	15.7
80°	36.2	33.8	25.3	18.1	9.6	7.2	7.2	6.1	6.1
82.5°	20.5	19.4	13.3	7.2	3.7	2.4	2.4	2.4	2.4
85°	8.5	7.2	4.8	2.4	1.3	1.3	1.3	1.3	1.3
87.5°	1.3	1.3	1.3	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)