

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580007

Luminaire Tested: **HCC4S20D010BZ-HM40525830-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S20D010BZ-HM40525830-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1979.3 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580007
CATALOG NUMBER: HCC4S20D010BZ-HM40525830-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580007

CATALOG NUMBER: HCC4S20D010BZ-HM40525830-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	125887	125887	125887
5°	132373	125711	121019
10°	137022	124221	115517
15°	141194	121963	110585
20°	141356	116941	104222
25°	136042	109299	97704
30°	126333	100582	91239
35°	113234	90557	84444
40°	99363	80798	78045
45°	86835	71537	71990
50°	76680	62595	64859
55°	67611	55504	58321
60°	60439	49116	51065
65°	53527	43225	43225
70°	46775	36857	36857
75°	39937	31215	34980
80°	31609	27916	31609
85°	20521	24059	29720



TEST NUMBER: P580007
 CATALOG NUMBER: HCC4S20D010BZ-HM40525830-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.7	4.9
10°-20°	272.3	13.8
20°-30°	381.5	19.3
30°-40°	393.0	19.9
40°-50°	334.6	16.9
50°-60°	247.9	12.5
60°-70°	155.6	7.9
70°-80°	77.3	3.9
80°-90°	20.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	750.5	37.9
0°-40°	1143.5	57.8
0°-60°	1726.1	87.2
0°-90°	1979.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1979.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1021	1021	1021	1021	1021	
5°	1069	1051	1015	986	977	103
15°	1106	1056	955	886	866	311
25°	1000	930	803	734	718	457
35°	752	696	601	562	561	469
45°	498	464	410	402	413	386
55°	314	290	258	263	271	284
65°	183	165	148	145	148	183
75°	84	75	66	71	73	90
85°	14	14	17	20	21	19
90°	0	0	0	0	0	



TEST NUMBER: P580007

CATALOG NUMBER: HCC4S20D010BZ-HM40525830-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1020.6	1020.6	1020.6	1020.6	1020.6	1020.6	1020.6	1020.6	1020.6
2.5°	1042.9	1039.0	1033.7	1024.5	1015.3	1007.5	999.6	995.7	994.3
5°	1069.1	1061.2	1050.8	1033.7	1015.3	999.6	986.5	980.0	977.4
7.5°	1087.4	1079.6	1062.5	1036.3	1010.2	986.5	965.5	956.4	953.7
10°	1094.0	1084.8	1061.2	1025.9	991.8	962.9	939.4	927.6	922.3
12.5°	1099.2	1087.4	1057.3	1015.3	973.5	938.0	913.1	897.4	893.5
15°	1105.7	1092.6	1055.9	1004.9	955.1	913.1	885.6	871.3	866.0
17.5°	1099.2	1084.8	1041.6	983.9	927.6	881.7	851.5	838.5	833.3
20°	1076.9	1061.2	1012.7	951.2	890.9	843.7	813.6	800.5	794.0
22.5°	1042.9	1025.9	976.1	910.5	849.0	803.1	774.3	761.1	757.2
25°	999.6	982.6	930.2	863.3	803.1	758.5	733.6	721.9	717.9
27.5°	948.6	931.5	880.4	814.9	757.2	715.4	695.7	683.8	681.3
30°	887.0	869.9	820.1	759.9	706.2	666.9	651.2	642.0	640.6
32.5°	818.8	804.4	758.5	703.6	652.4	619.7	607.9	601.4	600.0
35°	752.0	736.3	695.7	645.9	601.4	572.6	562.0	560.8	560.8
37.5°	683.8	668.1	635.4	589.6	551.6	525.3	521.4	522.7	522.7
40°	617.1	602.6	573.8	535.9	501.8	482.1	480.8	483.5	484.7
42.5°	554.2	542.4	516.2	483.5	454.7	438.8	440.2	445.5	449.4
45°	497.8	487.4	463.7	434.9	410.1	398.2	402.3	408.8	412.7
47.5°	446.8	437.6	415.3	389.1	368.2	360.3	365.5	373.3	378.6
50°	399.6	391.7	370.7	343.3	326.2	320.9	327.6	335.4	338.0
52.5°	357.6	349.8	327.6	304.0	290.9	288.2	294.8	301.3	305.2
55°	314.4	307.9	289.5	268.6	258.1	256.8	263.4	268.6	271.2
57.5°	279.1	272.5	255.4	237.1	227.9	226.6	233.2	237.1	238.5
60°	245.0	238.5	222.7	205.7	199.1	199.1	203.0	205.7	207.0
62.5°	213.6	207.0	192.6	178.1	173.0	173.0	173.0	174.2	178.1
65°	183.4	178.1	165.1	152.0	148.1	145.4	145.4	145.4	148.1
67.5°	155.9	150.7	140.2	128.3	124.4	120.5	119.2	121.8	121.8
70°	129.7	125.8	115.3	106.1	102.2	98.3	96.9	102.2	102.2
72.5°	106.1	102.2	95.7	86.5	82.6	81.2	83.8	86.5	87.7
75°	83.8	79.9	74.7	69.4	65.5	66.9	70.8	72.0	73.4
77.5°	62.9	61.6	56.3	52.4	52.4	53.7	56.3	59.0	60.2
80°	44.5	43.2	40.6	38.0	39.3	42.0	43.2	45.9	44.5
82.5°	27.5	27.5	26.2	26.2	27.5	30.2	31.4	32.8	34.1
85°	14.5	14.5	14.5	15.7	17.0	18.4	19.6	21.0	21.0
87.5°	3.9	5.3	5.3	6.5	7.9	7.9	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)