

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P571729

Luminaire Tested: **HCC4W20D010BZ-HM40525835-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P571729
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010BZ-HM40525835-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2093.7 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P571729
CATALOG NUMBER: HCC4W20D010BZ-HM40525835-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P571729

CATALOG NUMBER: HCC4W20D010BZ-HM40525835-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88	88	88	88
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67	67	67	67
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58	58	58	58
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52	52	52	52
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46	46	46	46
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41	41	41	41
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37	37	37	37
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34	34	34	34
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31	31	31	31

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	123938	123938	123938
5°	128943	125080	123730
10°	133164	126175	123457
15°	137836	126560	123444
20°	138297	123504	121903
25°	133416	117343	118268
30°	124154	109256	112347
35°	111834	99968	103642
40°	98606	90942	95096
45°	86207	81951	85980
50°	76335	73725	77659
55°	67159	65116	67740
60°	59946	55604	57282
65°	52681	45151	44392
70°	46054	33287	30366
75°	38173	20064	16203
80°	28910	7742	4830
85°	13445	1981	1981



TEST NUMBER: P571729
 CATALOG NUMBER: HCC4W20D010BZ-HM40525835-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.9	4.6
10°-20°	282.8	13.5
20°-30°	409.6	19.6
30°-40°	432.1	20.6
40°-50°	374.0	17.9
50°-60°	277.0	13.2
60°-70°	159.7	7.6
70°-80°	55.8	2.7
80°-90°	5.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	789.3	37.7
0°-40°	1221.4	58.3
0°-60°	1872.4	89.4
0°-90°	2093.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2093.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1005	1005	1005	1005	1005	
5°	1041	1028	1010	1002	999	100
15°	1079	1044	991	968	967	304
25°	980	931	862	857	869	449
35°	743	709	664	679	688	464
45°	494	481	470	488	493	384
55°	312	305	303	314	315	282
65°	180	170	155	147	152	180
75°	80	68	42	34	34	86
85°	10	5	1	1	1	15
90°	0	0	0	0	0	



TEST NUMBER: P571729

CATALOG NUMBER: HCC4W20D010BZ-HM40525835-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8
2.5°	1019.7	1016.9	1012.9	1007.4	1002.0	997.9	996.6	995.3	995.3
5°	1041.4	1036.0	1027.8	1016.9	1010.2	1006.0	1002.0	999.3	999.3
7.5°	1056.3	1050.9	1038.7	1023.7	1014.2	1006.0	1000.6	996.6	996.6
10°	1063.2	1056.3	1041.4	1022.3	1007.4	996.6	988.5	985.7	985.7
12.5°	1071.3	1063.2	1042.7	1018.3	999.3	985.7	977.6	974.8	974.8
15°	1079.4	1069.9	1044.1	1015.6	991.1	974.8	968.1	966.7	966.7
17.5°	1075.3	1063.2	1033.2	999.3	972.1	955.8	949.0	949.0	950.4
20°	1053.6	1041.4	1007.4	969.4	940.9	928.7	923.2	926.0	928.7
22.5°	1021.1	1006.0	969.4	932.7	902.9	892.0	892.0	896.2	900.2
25°	980.3	966.7	931.4	890.6	862.2	854.1	856.7	863.5	869.0
27.5°	934.1	919.2	882.5	844.5	816.0	812.0	818.7	828.2	830.9
30°	871.7	859.4	828.2	791.5	767.1	765.7	775.3	782.0	788.8
32.5°	812.0	798.3	768.5	733.2	715.5	716.9	727.8	735.9	739.9
35°	742.7	730.4	708.7	680.2	663.9	666.6	678.9	687.1	688.3
37.5°	677.5	669.4	647.6	625.9	613.6	619.2	629.9	639.5	639.5
40°	612.4	605.5	589.2	571.6	564.8	571.6	582.4	590.6	590.6
42.5°	549.9	545.9	532.2	520.0	515.9	525.4	535.0	541.7	540.4
45°	494.2	490.1	480.6	471.2	469.8	479.3	487.5	491.5	492.9
47.5°	444.0	441.3	433.1	426.3	426.3	435.9	442.6	446.6	448.0
50°	397.8	395.1	388.3	382.9	384.2	393.8	399.2	403.3	404.7
52.5°	351.7	350.3	344.9	338.0	342.2	348.9	355.7	358.4	359.8
55°	312.3	312.3	305.4	300.1	302.8	309.6	313.6	315.0	315.0
57.5°	277.0	275.6	267.5	262.1	263.4	270.2	272.9	274.2	274.2
60°	243.0	241.7	233.5	225.4	225.4	229.4	230.8	232.2	232.2
62.5°	210.5	209.1	199.6	192.8	190.1	188.7	188.7	191.4	196.8
65°	180.5	179.3	169.8	158.9	154.7	150.7	146.6	149.3	152.1
67.5°	153.5	150.7	141.2	131.7	122.2	115.4	108.6	112.6	118.1
70°	127.7	124.9	114.0	103.2	92.3	81.4	76.0	81.4	84.2
72.5°	103.2	100.5	89.6	78.8	65.1	54.3	53.0	54.3	55.6
75°	80.1	78.8	67.9	55.6	42.1	34.0	34.0	34.0	34.0
77.5°	59.8	57.0	46.1	35.3	24.4	19.0	17.7	17.7	17.7
80°	40.7	38.0	28.6	20.4	10.9	8.1	8.1	6.8	6.8
82.5°	23.1	21.7	14.9	8.1	4.1	2.8	2.8	2.8	2.8
85°	9.5	8.1	5.4	2.8	1.4	1.4	1.4	1.4	1.4
87.5°	1.4	1.4	1.4	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)